




Electrical Characteristics

Nominal Impedance:	75 ohms
Frequency Range:	DC to 2 GHz
Operating Voltage (rms):	250 V maximum at sea level

Mechanical Characteristics


Mating Cycles:	200 cycles minimum
----------------	--------------------

Environmental Characteristics

Temperature Range:	-55 °C to +85 °C
--------------------	------------------

	PART	DESCRIPTION
1	Body	Brass, nickel plated
2	Dielectric	Polypropylene
3	Contact	Brass, tin plated
4	Washer	Iron, nickel plated
5	Nut	Iron, nickel plated

Dimension & material update	KA	3	24 Sept 08
CAD Issue	SN	2	12 Dec 02
First Issue	CBB	1	05 Nov 99
DESCRIPTION OF REVISION	APPVD	ISS	DATE



Connectivity Solutions
7-13 Russel Way,
Widford Industrial Estate,
Chelmsford, Essex,
CM1 3AA, UK.
Tel: +44 (0) 1245 359515
Fax: +44 (0) 1245 358938

SCALE: Not To Scale	DRAWN BY:	S Nash	TITLE: F Bulkhead Jack to Jack Adaptor	PART NUMBER:
DIMENSIONS: mm	CHECKED BY:	P Couzens		VFA340
TOLERANCES: ± 0.2mm unless otherwise stated	APPROVED BY:	P Couzens		
	DATE:	12 Dec 02		