

PERFORATION
1/8" CUT, 1/32" SPACE TYP.
2.000" REPEAT.

LINER SLITS

.750 [19.05] TYP.

1.000 [25.40] TYP.

2.00 TYP.
[50.80]

1.500 [38.10]
TYP. 4 PLCS.
1.700 [43.18] TYP.

7.6 ±.031 [193.55 ±0.10]

PART NUMBER	MATERIAL	MARKER SIZE inches (mm)	LABELS PER ROW	ROWS PER FANFOLD	STANDARD PKG. QTY.
C150X075YJD	GMY	1.500" [38.10] X .750" [19.05]	4	12	5000

PANDUIT CORP. TINLEY PARK, ILLINOIS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) .031 (.XXX) .005
(.XX) .015 ANGLES

DRAWN BY	RVU
----------	-----

SCALE 1/2

DATE	9-29-04
------	---------

DRAWING NO.

C10233

DWG
A
SIZE

0	9-29-04	RVU		DRAWING RELEASED.	0000	R		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP