


USB Connector A Type Receptacle Right Angle Single Deck (SMT)

154-UAR42-E

KOBICONN

USB Connector A Type Receptacle Right Angle Single Deck (SMT)

154-UAR42-E



Dimensions: mm

Electrical Specifications

Contact Resistance:	30 milliohms max.
Dielectric w/standing Voltage:	750 VAC
Insulator Resistance:	1,000 Megaohms min.
Current Rating:	1.0 Ampere max. @ 30°C
Durability:	1500 Cycles
Temperature Range:	-55°C to +85°C
Voltage:	30 VAC

SPECIFICATIONS

Part Name	Item	Qty.	Material
Contacts:	3	4	Copper Alloy/Selective Gold Plating: 2 - Aμ5μ"; 5 - Aμ30μ"
Housing:	2	1	Thermoplastic, Glass filled, 240°C
Shell:	1	1	Copper Alloy/ Tin-Lead Plated over Copper
RoHS Compliant			

Date Last Revised: 6/3/10

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301006

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-UAR42-E](#)