

ARC Reticulated Foam Series

ARC- RT- 10448

Description: Flexible, low density, high loss, carbon impregnated foam.

Standard Thickness: 2.000" (50.8mm)

Standard Sheet Size: 24" x 24" (60.96 x 60.96cm)

Density: 5 lbs/cu ft (80 kg/M³)


Resistance: 300 ohms/sq

Color: Black

Temp. Range: -70°F to + 250°F (-56.7°C to 121.1°C)

Features:

- PSA: A high performance unsupported acrylic transfer film adhesive is available. PSA thickness is .002" (0.51mm)
- Top Coat: Tough acrylic sealant (optional)
- Ground Film: Conductive Mylar when specified



Solutions for Interference Control

ARC Technologies, Inc.
 11 Chestnut Street, Amesbury, MA 01913
 978-388-2993 Fax: 978-388-6866
www.arc-tech.com