



Sample photo

Order symbol: PCM 95/60 G
Product nbr: 6016331
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074054777
El. number:
Finland: 3421392
Electric No. 8212027569
Denmark:
Electric No. Sweden: 2535300

Including: Base with metric knock-outs and PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:	
mm:	100	100	60	MIN 8 DIN-15 Mounting rail
inch:	3.9	3.9	2.4	B-3 DIN-35 Mounting rail
				FP 22046 Wall fastening lug (4 pcs)
Materials:			Rating:	
Material:	Polycarbonate			
Base colour:	RAL 7035 -light grey			
Cover screws material:	Polyamide			
Cover colour:	RAL 7035 -light grey			
Cover screws colour:	Grey			
Gasket material:	Polyurethane			
Temperatures:			Ingress Protection (EN 60529): IP66/67	
Temperature °C (short term):	-40 ... 120 °C		Impact Resistance (EN 62262): IK08	
Temperature °C (continuous):	-40 ... 80 °C		Electrical insulation: Totally insulated	
Temperature °F (short term):	-40 ... 250 °F		Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (continuous):	-40 ... 175 °F		UV resistance: UL 508	
Accessories:			Flammability Rating: UL 746C 5V	
MIV 95			Glow Wire Test (IEC 695-2-1) °C: 960	
			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
			Certificates:	
			Germanischer Lloyd (GL)	
			SGS Fimko	
			Gost R	

