

ELECTRO-ACOUSTIC TRANSDUCER



ROHS COMPLIANT AVAILABLE UPON REQUEST

PART NUMBER:
BRT1209PF-05-RA

SPECIFICATIONS:

RATED VOLTAGE:	5 VDC
OPERATING VOLTAGE:	4 ~ 8
MAX CURRENT:	40 mA
SOUND OUTPUT LEVEL:	85dB @ 10 cm
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	2400 Hz
OPERATING TEMPERATURE:	-40 TO +85°C
TONE MODE:	CONTINUOUS
PULSE RATE:	N/A
COIL RESISTANCE:	45 ± 5
COIL IMPEDANCE:	80
FRAME DIAMETER:	12.0 mm
FRAME DEPTH:	9.5 mm
MOUNTING DIMENSIONS:	6.5 mm

COMMENTS:

*VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

**VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

DIMENSIONS:

