

42" Class Viera® S2 Series 1080p Plasma

FIND ANOTHER MODEL ▶

Model number: TC-P42S2

12 Reviews

Print this | Share this

Product no longer available for purchase.

- 42" Class Viera® S2 Series 1080p Plasma (41.6" Diagonal)
- 1080 TV Lines Moving Picture Resolution
 - VIERA Image Viewer™ (Photo)
 - Clean Touch Bezel Design
 - ENERGY STAR Qualified

Online Order Assistance

- Track your order
- Print your invoice
- Read our shipping FAQs
- Register your product

Accessories

- Find accessories for your product

Contact Us

- Live Chat
- Phone
- Email
- Mail
- International Support

Operating Manuals	Help & Tutorials	FAQs	Tech Specifications	Warranty & Care Plans	Accessories	Drivers & Downloads
Model Type	Plasma					
Series	S2					
Model Year	2010					
VIDEO	.					
Screen Size	42" Class (41.6" diagonal)					
Contrast Ratio	Native: 2,000,000:1					
Aspect Ratio	16:9					
Native Resolution (Number of Pixels)	2,073,600 (1,920 x 1,080)					
Moving Picture Resolution	1080 lines					
Shades of Gradation	6,144 equivalent					
HDTV Display Capability (1080p, 1080i, 720p)	Yes					
EDTV Display Capability (480p)	Yes					
Aspect Control	Normal, Just, Zoom, Full, H-fill					
Full HD 3D	No					
AR (Anti-Reflective) Filter	Yes					
600Hz Sub-field Drive	Yes					
24p Cinematic Playback	No					
24p Playback(2:3)	Yes					
Deep Color	Yes					
x.v.Color	Yes					
Studio Ref Mode	No					
Pro Setting	No					
THX Mode	No					
ISFccc	No					
3D Color Management	Yes					
Sub Pixel Control	No					
Motion Pattern Noise Reduction	Yes					
600 Hz Sub-field Drive	Yes					
AUDIO	.					
Speakers	Full-range x 2 (L, R)					
Number of Speakers	2					
Audio Output	20 W (10% THD)					
BBE® VIVA HD3D Sound	No					
Surround Sound	Yes					
INPUTS & JACKS	.					
Integrated ATSC Tuner	Yes					
VIERA Image Viewer™	Y (JPEG playback)					
HDMI Input	3 (1 side)					
Composite Video Input	2 (1 side)					
Audio Input (for Video)	2 (1 side)					
PC Input	No					
Component Video Inputs (Y, PB, PR)	2					
Audio Input (for Component Video)	2					
RS232C	No					
Digital Audio Output	1					
HDMI Input-Support Feature	Audio Return Channel (Input 1)					
Analog Audio Input (for HDMI/DVI)	Yes					
USB	No					
LAN Port	No					
CONVENIENCE	.					
VIERA Link™	Yes					
VIERA Cast™ (IPTV)	No					
VIERA® Tools	Yes					
Game Mode	Yes					
3D Active Shutter Eyewear	No					
Clean Touch Bezel	Yes					
Pixel Orbiter (Anti-Image Retention)	Yes					
Built-In Closed Caption Decoder	Yes					
Off - Timers	Yes					
Trilingual Menu	English/Spanish/French					
GENERAL	.					
Power Supply	AC 120 V, 60Hz					
Rated Power Consumption	298 W					
Standby Power Consumption	0.3 W					
Energy Star	Yes					
Receiving System	ATSC/QAM/NTSC					
Operating Temperature	32°F - 104°F (0°C - 40°C)					
Safety Standard	UL6500/C-UL					
Swivel Angle	No					
Optional Wall-mounting Bracket	TY-WK4P1RW					
SPECIFICATIONS	.					
Dimensions (H x W x D) with Stand	27.8" x 40.6" x 12.1"					
Dimensions (H x W x D) without Stand	26.1" x 40.6" x 3.7"					
Weight (lbs.) w/Stand	55.1 lbs.					
Weight (lbs.) without Stand	50.7 lbs.					
Carton Dimensions	30.2" x 45.6" x 11.2"					
Gross Weight [lbs (kg)]	70.5 lbs.					