




PRODUCT NUMBER
76342-YXXXLF


- RoHS COMPATIBLE, SEE NOTE 5
- OPTIONAL LETTER
H: HIGH TEMPERATURE PRODUCT.
C: PACKAGED IN SHORT TUBE.
- NUMBER OF POSITIONS PER ROW: 02 TO 50.
PLATING CODE
3= 0.76µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.
- 4= 2µm MIN MATTE TIN FULL PLATED
1.27µm Ni MIN UNDERPLATING



NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED FLAME RETARDANT PER UL 94 V-0
LOW TEMPERATURE: COLOR BLUE
HIGH TEMPERATURE: COLOR GREY.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.
5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.
- 4 - TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: (N x 2.54) - 0.08 = 20.24 mm
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ± 5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
- MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
- 6 - END STAND-OFFS FOR 2x2 UP TO 2x5 POS
NO END STAND-OFFS FOR 2x6 UP TO 2x50 POS

mat'l. code SEE NOTES 1 & 2		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection mm		product family DUBOX	
lfr		ecn no		dr		date		title	
S		F10342		DLE		01.06.12		BtB RECEPT.	
T		F04-0347		DLE		04.09.27		VERT DR TMT	
U		F06-0137		DLE		06.02.27		scale 5:1	
V		F06-0204		DLE		06.06.20		dr	
W		F11-0043		JCO		12.02.22		enr	
X		B-19123		LMU		14.10.21		chr	
Y		B-21211		AMA		15.06.22		appd	
sheet		revision		Y		C		dwg no	
index		sheet		1		2		76342	
								sheet 1 of 2	
								size	
								A3	
								type	
								CUSTOMER Drawing	



Copyright FCJ

mat'l. code SEE SHEET 1				surface ISO 1302 <input checked="" type="checkbox"/>		tolerance ISO 406 ISO 1101		projection 		product family DUBOX	
ltr				ecn no		dr		date		title	
A				F04-0347		DLE		04.09.27		BtB RECEIPT. VERT DR TMT	
B				F06-0204		DLE		06.06.20			
C				B-21211		AMA		15.06.22			
				angles		linear		±0.3		mm	
				±2'				scale 5:1			
				dr		D LEGRAND		04.09.27		dwg no	
				engr		P NIZZI		04.09.27		sheet 2 of 2	
				chr		D LE		04.09.27		size	
				appd		P NZ		04.09.27		A4	
sheet index		revision sheet								type CUSTOMER Drawing	

form: A4