

Crimping pliers - CRIMPFOX 25R - 1212039

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for ferrules as per DIN 46228 section 1+4, 10-25 mm², insertion from the side, WM crimp

Why buy this product

- ✓ Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25%

Key commercial data

Packing unit	0
Minimum order quantity	1
Catalog page	Page 271 (CL2-2011)
GTIN	 4 046356 453905
Custom tariff number	82032000
Country of origin	SWEDEN

Technical data

General

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm
Weight	578 g
Die station	Crimping position 1
Max. cross section	10 mm ²
AWG max	8
Die station	Crimping position 2
Max. cross section	16 mm ²
AWG max	6
Die station	Crimping position 3
Max. cross section	25 mm ²
AWG max	4
Die station	Crimping position 4
Die station	Crimping position 5
Compression	WM crimp

Crimping pliers - CRIMPFOX 25R - 1212039

Technical data

General

Type of contact	Ferrules
-----------------	----------

Classifications

eclass

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

etim

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186

unspsc

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 
--

Crimping pliers - CRIMPFOX 25R - 1212039

Accessories

Accessories

Tools

Replacement die - CRIMPFOX 25R/DIE - 1212040



Spare die for CRIMPFOX 25R

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring