

Shape 1:1

KPE-165



926978

KPE-151




926878

KPE-150




KPE-110



926980


KPE-120




Model Number	KPE-165	KPE-151	KPE-150	KPE-110	KPE-120
Operating Voltage (Vp-p maximum)	30	20	15	30	30
Sound Pressure Level at 10cm/10Vp-p (dB, minimum)	85 at 4.8KHz	80 at 4.0KHz	87 at 5.0KHz	90 at 4.1KHz	88cb at 6.0KHz
Current Consumption at 10Vp-p square wave (mA, maximum)	8 at 4.8KHz	13 at 4.0KHz	11 at 5.0KHz	10 at 4.1KHz	8 at 4.1KHz
Capacitance (± 30% pF)	15,000	30,000	21,000	25,000	12,000
Operating Temperature (°C)	-20~+60	-20~+60	-20~+60	-20~+60	-20~+60
Storage Temperature (°C)	-30~+70	-30~+70	-30~+70	-30~+60	-30~+70
Weight (Gram)	1	0.4	1	2.2	3.0
Packing Quantity (PCS/BOX)	1,000	1,000	1,200	500	500

Dimension


KPE-165




KPE-151




KPE-150



KPE-110



KPE-120



Frequency Curve

