

© COPYRIGHT 1975 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

UNPUBLISHED WORK
REPRODUCED WITHOUT PERMISSION
OF AMP INCORPORATED

207226-1 1. AS SHOWN, $\triangle 5$
2. WITH 3-40 POSITION CRIMP MODULES.

207226-2 1. SAME AS -1 EXCEPT:
2. WITH 3-40 POSITION DISPLATION MODULES.

OBSELETE SAME AS -1 EXCEPT:
2. AMP PART NUMBER INK STAMPED ON EITHER
SIDE OF HOUSING

OBSELETE SAME AS -1 EXCEPT:
2. FOR CABLE .395-.600 DIA.

REVISIONS					
A	P	F	ZONE	LTR	DESCRIPTION
					RELEASED
					ADD OVERALL DIM'S, E-397
					ADDED -3 PER ECN H-737
					ADDED -4 PER ECN R-1490
					OBS. -3 & -4 / ECN R-2520
					REV PER 0630-0401-03 CT

DATE APPROVED

11/4/75 JLB


4-27-76 JLB

5-12-79 JLB

9-17-85 JLB

1-21-87 MPH

2-04 CT



- ① 40 POSITION CRIMP MODULES ACCEPT "F" CRIMPED CONTACTS,
(CONTACTS NOT SUPPLIED, MUST BE ORDERED SEPARATELY).
- ② 40 POSITION DISPLATION MODULES ARE SUPPLIED WITH CONTACTS.
- ③ MAT'L-ALL PARTS: GLASS FILLED BLACK THERMOPLASTIC.
- ④ ALL ASSY SCREWS ARE STEEL, ZINC PLATED.
- ⑤ FOR CABLE .750 - 1.000 DIA.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .010 ANGLES ± .5°		CONTRACT NO		PART NO	
MATERIAL $\triangle 3 \triangle 4$		DR <i>JLB</i> 12/4/75		NAME	
FINISH		CHK <i>Estimate</i> 12-16-75		CABLE KIT, SIZE I, 120 POSITION, ZERO ENTRY CONN., SERIES "CR"	
		APPD <i>JLB</i> 12-10-75		SIZE CODE IDENT NO DRAWING NO	
		APPD <i>A Miller</i> 12-16-75		C 00779 207226	
		DSGN APPD		SCALE	
		OTHER APPD		"CR" SHEET 1 OF 1	