




Underground® Model 60® & Model 64® Combo Pack, Card of 10



Product Resources

[WeatherProof™ and UnderGround™ Wire Connectors Brochure](#)
(PDF | 1782K)

[Underground® MSDS](#)
(PDF | 152K)

[IDEAL Connector UL Listed Wire Combinations](#)
(PDF | 378K)

Features

- Smallest wet location/direct burial connector with widest wire range
- Model 60® Handles wire sizes from #20 to #10 AWG copper
- Model 60® Minimum of 1 #20 with 1 #18
- Model 60® Maximum of 2 #12 & 1 #10 AWG
- Model 64® Handles wire sizes from #18 to #8 AWG copper
- Model 64® Minimum of 2 #18 AWG
- Model 64® Maximum of 2 #10 AWG
- Non-hardening sealant completely seals out moisture to protect against fungus and corrosion
- Sealant is stable down to -40 deg.C
- Swept-wing design for comfort
- Live-action, square-wire spring
- Hexagonal shape for standard nutdriver
- UL Listed and CSA Certified
- Shell rated for 105° C
- Flame-retardant shell

Models

Description	Catalog #
Underground® Model 60® & Model 64® Combo Pack, Card of 10	30-6064