



2 Surface and Thru Hole Mount Coin Cell Retainer Contacts



Material: Phosphor bronze, nickel plate.

| Stock No. | Mfr.'s Type | Cell Dia. | A      | B      | C      | Battery Reference              | PER PK./100 |
|-----------|-------------|-----------|--------|--------|--------|--------------------------------|-------------|
| 839-3010  | 3000        | 12 mm     | 0.520" | 0.770" | 0.118" | BR1216, BR1220, BR1225         | 22.58       |
| 839-3011  | 3002        | 20 mm     | 0.821" | 1.220" | 0.145" | BR2016, BR2020, BR2025, DR2032 | 22.30       |

Thru Hole Mount Coin Cell Battery Holders




Contacts: Spring steel, nickel plate over copper. Base: UL 94V-0 PBT.

| Stock No. | Mfr.'s Type | Fig. | Cell Dia. | No. Cells | A      | B      | C      | Battery Reference              | EACH |
|-----------|-------------|------|-----------|-----------|--------|--------|--------|--------------------------------|------|
| 839-0500  | 500         | 1    | 12 mm     | 1         | 0.593" | 0.393" | 0.312" | BR1216, BR1220, BR1225         | 1.17 |
| 839-0502  | 502         | 1    | 16 mm     | 1         | 0.750" | 0.463" | 0.312" | CR1616, CR1620, CR1632         | 1.16 |
| 839-0103  | 103         | 2    | 20 mm     | 1         | 0.896" | 0.807" | 0.335" | BR2016, BR2020, BR2025, BR2032 | .72  |
| 839-1026  | 1026        | 2    | 20 mm     | 2         | 1.093" | 0.807" | 0.452" | BR2016, BR2020, BR2025, BR2032 | .79  |
| 839-3000  | 104         | 2    | 23 mm     | 1         | 1.000" | 0.807" | 0.335" | BR2320, BR2325, BR2330, BR2335 | .72  |
| 839-1027  | 1027        | 2    | 23 mm     | 2         | 1.093" | 0.807" | 0.452" | BR2320, BR2325, BR2330, BR2335 | .79  |
| 839-1025  | 1025        | 2    | 24 mm     | 2         | 1.093" | 0.807" | 0.452" | CR2430, CR2450                 | .79  |
| 839-0301  | 301         | 2    | 30 mm     | 1         | 1.297" | 0.807" | 0.335" | BR2032                         | .72  |

Surface Mount Coin Cell Battery Holders


20 mm Holders. Contacts: Spring steel, tin over nickel plate. Base: UL 94V-0 nylon, stanyl-46.



| Stock No. | Mfr.'s Type | No. Cells | A      | B      | C      | D      | Battery Reference               | EACH |
|-----------|-------------|-----------|--------|--------|--------|--------|---------------------------------|------|
| 839-1061  | 1061        | 1         | 0.256" | 0.286" | 1.015" | 0.156" | CR2016*, CL2020, CR2025, CR2032 | .97  |
| 839-1062  | 1062        | 2         | 0.375" | 0.406" | 1.015" | 0.156" | CR2016†, CL2020, CR2025, CR2032 | .97  |


\*For 1 or 2 cells. †For 3 cells.

9 V Battery Holders




| Stock No. | Mfr.'s Type | Fig. | Material     | Type             | Termination           | EACH |
|-----------|-------------|------|--------------|------------------|-----------------------|------|
| 839-1294  | 1294        | 1    | Glass-filled | Universal Holder | PC Terminals          | .81  |
| 839-1295  | 1295        | 2    | Glass-filled | Universal Holder | Quick-Fit/Solder Lugs | .78  |
| 839-4055  | 1291        | 3    | Aluminum     | Snap-In Holder   | PC Lugs               | 1.28 |
| 839-4050  | 1290        | 4    | Aluminum     | Snap-In Holder   | Solder Lugs           | 1.24 |

9 V Battery Snap-Ons



| Stock No. | Mfr.'s Type | Fig. | Material         | Termination                 | PER PK./100 |
|-----------|-------------|------|------------------|-----------------------------|-------------|
| 839-0968  | 968         | 1    | Fibre            | PC Pins                     | 59.00       |
| 839-2027  | 68          | 2    | Fibre            | Without Pins or Leads       | 20.22       |
| 839-0593  | 593         | 3    | Steel, Tin Plate | For Mounting Battery on PCB | 19.00       |
| 839-0594  | 594         | 4    | Steel, Tin Plate | For Mounting Battery on PCB | 24.18       |

9 V Battery Straps




| Stock No. | Mfr.'s Type | Fig. | Material       | Lead Length | Type              | PER PK./100 |
|-----------|-------------|------|----------------|-------------|-------------------|-------------|
| 839-3085  | 2238        | 1    | Rigid Vinyl    | 4.00"       | Premium Insulated | 35.20       |
| 839-3086  | 2239        | 1    | Rigid Vinyl    | 6.00"       | Premium Insulated | 37.73       |
| 839-3087  | 2240        | 1    | Rigid Vinyl    | 8.00"       | Premium Insulated | 37.50       |
| 839-3088  | 2241        | 2    | Rigid Vinyl    | 4.00"       | Premium Insulated | 37.50       |
| 839-3089  | 2242        | 2    | Rigid Vinyl    | 6.00"       | Premium Insulated | 27.02       |
| 839-3090  | 2243        | 2    | Rigid Vinyl    | 8.00"       | Premium Insulated | 41.08       |
| 839-3100  | 232         | 3    | Flexible Vinyl | 4.00"       | Economy Insulated | 24.67       |
| 839-3101  | 233         | 3    | Flexible Vinyl | 6.00"       | Economy Insulated | 25.29       |
| 839-3102  | 234         | 3    | Flexible Vinyl | 8.00"       | Economy Insulated | 24.30       |
| 839-3103  | 235         | 4    | Flexible Vinyl | 4.00"       | Economy Insulated | 25.40       |
| 839-3104  | 236         | 4    | Flexible Vinyl | 6.00"       | Economy Insulated | 25.80       |
| 839-3105  | 237         | 4    | Flexible Vinyl | 8.00"       | Economy Insulated | 27.44       |

| Stock No. | Mfr.'s Type | Fig. | Material     | Lead Length | Type                  | EACH |
|-----------|-------------|------|--------------|-------------|-----------------------|------|
| 839-3091  | 72-4        | 6    | 0.062" Fibre | 4.00"       | Premium               | .55  |
| 839-2028  | 72          | 6    | 0.062" Fibre | 6.50"       | Premium               | .56  |
| 839-3093  | 72-8        | 6    | 0.062" Fibre | 8.00"       | Premium               | .57  |
| 839-3094  | 83-4        | 7    | Fibre        | 4.00"       | Premium Insulated     | .77  |
| 839-2029  | 83          | 7    | Fibre        | 6.50"       | Premium Insulated     | .78  |
| 839-3096  | 83-8        | 7    | Fibre        | 8.00"       | Premium Insulated     | .79  |
| 839-3097  | 85-4        | 8    | Fibre        | 4.00"       | Premium Insulated     | .81  |
| 839-3098  | 85-6        | 8    | Fibre        | 6.50"       | Premium Insulated     | .82  |
| 839-3099  | 85-8        | 8    | Fibre        | 8.00"       | Premium Insulated     | .83  |
| 839-3106  | 227         | 5    | Fibre        | 7.00"       | Dual-Parallel Circuit | 1.34 |
| 839-3107  | 229         | 5    | Fibre        | 7.00"       | Dual-Series Circuit   | 1.34 |

Shielded 9 Volt Battery Straps

- Insulates and Shields 9 Volt Battery Snap-On Connector Contacts
- Assures Safe Secure Use, Reduces the Potential of Short Circuits and Prevents Tampering with Battery Contacts
- Protects Circuits and Sensitive Electronic Equipment, Prevents Unwanted Electrical Discharge Due to Unintended Grounding
- Protects Battery Contacts From Dust, Dirt, and Physical Damage
- Ideal for Rugged Applications. Constructed of High Impact Molded Plastic with Integral Wire Lead Strain Relief
- Male and Female Snap-On Contacts Assure a Positive Battery Connection and a Low Contact Resistance

Specifications. Base: Polypropylene. Male/Female Contacts: Brass, nickel plate. Wires (Red and Black): #26 AWG, tinned, 0.187 end strip. UL/CSA 1007.



| Stock No. | Mfr.'s Type | Lead Length  | PER PK./100 |
|-----------|-------------|--------------|-------------|
| 839-3108  | 84-4        | 4.00" ±0.250 | 27.40       |
| 839-3109  | 84-6        | 6.00" ±0.250 | 29.23       |
| 839-3110  | 84-8        | 8.00" ±0.250 | 28.90       |