





CERTILOK - Die Set

0.2 0.5 1.5
0.25 0.75 2.5 4
0.5 1.0
mm

View X

Die set used with basic hand tool P/N 169400-0.
See instruction sheet 408-6764

Spare contact locator available P/N 2-539785-4

Basis HDZG Basic Handtool	Profil Profile	Kontakt Contact	DGB (mm ²) Wire Range	ISO Ø INS. Range	Draht CH Wire CH ±0.05	Draht CW Wire CW
169400-0	1	964321	0.2-0.5	1.15-1.6	1.18	1.78
	1	969008	0.2-0.5	1.15-1.6	1.18	1.78
	2	964323	0.5-1.0	1.4-2.1	1.45	2.03
	2	964303	0.5-1.0	1.4-2.1	1.45	2.03
	3	964325	>1.0-2.5	2.2-3.0	1.8	2.79
	3	964305	>1.0-2.5	2.2-3.0	1.8	2.79
	4	964327	>2.5-4.0	3.3-4.5	2.35	3.20
	4	964307	>2.5-4.0	3.3-4.5	2.35	3.20

THIS DRAWING IS A CONTROLLED DOCUMENT OF AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING DEPARTMENT SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWB K. Czech 07 JUL 98	Tyco Electronics 64625 Bensheim (Germany)			
DIMENSIONS: mm - DIN 7168m		CHK J. Reuter 10 JUL 98	NAME Matrizensatz DIE SET (for SPT and TAB 4.8mm)			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	PRODUCT SPEC			
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES		APPLICATION SPEC	SIZE A3			
MATERIAL -		WEIGHT -	CAGE CODE 00779			
FINISH -		CUSTOMER DRAWING	DRAWING NO C=539615-1			
		SCALE 2:1	SHEET 1 of 1			
			REV A			