

PRO-CRIMPER™ II Hand Tools and Dies



- Ratchet Control Provides Complete Crimping Cycle
- Emergency Ratchet Release
- Angled Head Provides a Comfortable Hand and Wrist Position
- One Tool with Interchangeable Die Sets Can Crimp Many Different Types of Connectors
- Accommodates Multiple Terminal Sizes in One Die Set
- Precision Construction of Durable High-Carbon Steel
- Extra Strength Pivot Pins Provide Greater Durability
- Produced Under a Quality Management System Certified to ISO 9001

Stock No.	Mfr.'s Type	Description	EACH
512-2599	354940-1	Hand tool frame without die sets	102.00

Stock No.	Mfr.'s Type	Crimps Connector Type	RG/U Cable or Wire Size	EACH
512-8614	58436-1	50 ohm BNC/TNC/N-type	58, 62, 59	55.64
512-2002	58436-3	50 ohm BNC	174, 188, 316, 179, 161, 187	55.64
512-2047	58436-2	50 ohm BNC	Belden 8281, 9141	55.64
512-2009	58425-2	75 ohm BNC	179, 161, 187	47.29
512-2038	58425-1	75 ohm BNC	62, 59	47.29
512-2071	58425-3	75 ohm BNC	Double braid 59, Belden 8281, 9141	47.29
512-2071	58425-3	75 ohm BNC	8, 213, 11, 216, 9, 214	69.55
512-9808	58485-1	50 ohm N-type	174, 316, 188, 179, 161, 187,	83.30
512-2501	58489-1	50 ohm military SMB	RD316, 188 double braid	
512-8748	58423-1	Insulated terminals	22-10 AWG	55.64
512-9812	58545-1	Uninsulated terminals	22-10 AWG	133.45
512-9813	58448-3	D-sub 20DF pin and sockets	28-20 AWG	132.60
512-9814	90800-2	D-sub 22DF pin and sockets	28-20 AWG	148.75
512-8952	90872-2	Soft shell .093 pin and pockets	24-18 AWG	119.00
512-8954	90871-2	Soft shell .093 pin and sockets	20-14 AWG	119.00
512-8942	90870-2	Soft shell .062 pin and sockets	30-24 AWG	119.00
512-8944	90869-2	Soft shell .062 pin and sockets	24-18 AWG	119.00


Production Hand Tool Kits



All kits include a carrying case with blade replacement kit and a small screwdriver.



Stock No.	Mfr.'s Type	Description	EACH
512-5835	231666-9	Carrying Case, Blade Replacement Kit, Screwdriver Only	45.08
512-5840	1-231666-0	Includes 8-Position Hand Tool and 4- and 6-Position Die Set	195.45
512-5845	1-231666-1	Includes 8-Position Hand Tool 4- and 6-Position Die, 4-Position Handset Die	231.12

D-Sub Pin and Socket Contact Extraction and Insertion Tools



Stock No.	Mfr.'s Type	Fig.	Description	EACH
512-9045	91067-1	A	M81969/1-04, for size 22	5.87
512-9110	91067-2	A	M81969/1-02, for size 20	5.87
512-9470	91285-1	B	For size 20 crimp and solder	21.42

IC Socket Tools



Stock No.	Mfr.'s Type	Fig.	Description	EACH
512-9815	58113-1	C	5 blade PGA extraction tool	12.97
512-9816	58113-3	C	10 blade PGA extraction tool	13.75
512-9817	58113-4	C	13 blade PGA extraction tool	17.14
512-9818	58113-5	C	16 blade PGA extraction tool	20.20
512-9820	58417-2	D	17 × 17 to 25 × 25 PGA insertion/extraction tool	300.17

AMPLIMITE® HDP-20 Subminiature D Multi-Position Repair Kit



Designed to cover on site repairs of the more popular Subminiature D connector applications. **Each Kit Contains:** 100 socket contacts; 100 pin contacts; 3 of each receptacle (9, 15, 25, and 37 pos.); 6 of each plug (9, 15, 25, and 37 pos.); 6 of each cable clamp (9, 15, 25, and 37 pos.); 1 insertion/extraction tool.

512-9057. 787054-1. Kit without crimp tool...EACH 181.90

BNC Premise Wiring Kit



Includes PRO-CRIMPER™ II hand tool, BNC plugs 5 RG-58, 10 RG-59/62, 5 RG-58 plenum and RG-59/62 plenum sizes; adapters — 2 jack-to-jack and 2 "T".

512-8477. 58477-1EACH 150.09

PIDG® and PLASTI-GRIP® Terminal Kit with PRO-CRIMPER™ II Hand Tool



Includes hand tool, 225 insulated ring and spade terminals in 12-10, 16-14, and 22-16 AWG wire sizes.

512-9236. 55823-1EACH 127.50

Heat Shrink Tubing Kit

Kit contains 103 pieces of tubing in assorted colors, 3/32 to 1/2 dia. × 6" length. Packaged in a sturdy plastic hinged lip case.

512-9824. 607243-1EACH 40.92