



UNIVERSAL CONNECTORS WITH
SUPERIOR PERFORMANCE

Posi-Twist™

NON IN-LINE CONNECTIONS



Posi-Twist™ Connectors



Part #	Gauge	L1	L2
PT2026 (Gray)	20-26	.696"	.285"
PT1424 (Orange/Blue)	14-24	.793"	.385"
PT1022 (Red/Yellow)	10-22	.965"	.505"
Material: Nylon 66 Temp: 120° C			

NOW AVAILABLE!
100 pc Posi-Twist™ boxes



Posi-Twist™ Connectors are also available in 20 pc and 4 pc packages as well as mixed assortments and **ASSORTMENT KITS.**

Gray Strip 1/2"		Orange/Blue Strip 5/8"		Yellow/Red Strip 11/16"	
Wires	Gauge	Wires	Gauge	Wires	Gauge
1 to 2	#18	1	#12	1	#8
2	#20	2	#14	2	#10
2 to 4	#22	2 to 3	#16	2 to 4	#12
2 to 5	#24	2 to 4	#18	2 to 5	#14
2 to 6	#26	2 to 5	#20	2 to 6	#16
		2 to 6	#22	2 to 7	#18
		2 to 8	#24	2 to 8	#20
				2 to 10	#22

* Plus countless multi-gauge wire combinations.

Posi-Lock™ Connector, Posi-Twist™ Connector, Posi-Plug™ Connector, Posi-Tite™ Connector, and Posi-Products™ are trademarks of Swenco® Products, Inc.
PATENTS: BREVETS: PATENTES: 5,228,875; 5,695,369; 5,868,589; 6358103B1;
Jap 2881414; Aus 708700; 729018; Tia 103534; Can 2,204,826; Mex 200626;
China ZL97105562.9 — Others pending
Copyright © 2002 Swenco® Products, Inc.

Unlimited Uses! ✓

- Oxygen Sensors
- Military Vehicles
- Boats
- Marine Equipment
- Pumps
- Gauges
- Outdoor Lighting
- Car Alarms
- Locks
- Lawnmowers
- Farm Equipment
- Ceiling Fans
- Car Stereos
- ... and much more!