

- FAQ's
- How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click  to remove) Search Tips

Your search criteria matched only one product, shown below

- Colour -specific keys mechanically and visually distinguish connections to prevent positive and negative unintentional insertion into unlike keyed or non -keyed ports and allows design flexibility and versatility for a more discrete network
- Factory terminated and 100% tested for insertion loss (all) and return loss (10Gig™ and SM). Assures high performance for increased up -time and lower cost of ownership
- Low smoke zero halogen meets IEC -60332 (LSZH) flame rating for standard compliant safety
- Singlemode endfaces UPC polished (55dB min. return loss) ensures a high quality endface for higher return loss to meet application requirements
- Every singlemode endface is 100% factory inspected in compliance with Telcordia GR -326-CORE, Issue 3 requirements to assure high performance
- Keyed LC 10Gig™ Patch Cords and Pigtails are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10Gb/s for link lengths up to 300 meters for OM3 at 850nm to assure high performance and reliability
- Test data supplied with each patch cord and pigtail establishes a performance reference to

streamline maintenance and troubleshooting

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.

Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

■ Part Number	FXLE10K10KM3
■ RoHS Compliance Status	RoHS directive is not applicable
■ Note	Intended for use in fixed installations which are outside the scope of RoHS
■ Part Description	LC (keyed K - slate) to LC (keyed K - slate) LSZH, multimode duplex patch cord, 10 GbE, 1.6mm jacketed cable (one duplex keyed LC connector on each end)- 50/125μ m
■ Product Type	Keyed LC LSZH Patch Cords
■ Length (m)	3
■ Fiber Compatibility	10 GbE 50/125μ m
■ Fiber Cable Size	1.6mm
■ Fiber Cable Type	Jacketed
■ Connector 1 Type	LC Connector - Keyed K (Slate)
■ Connector 2 Type	LC Connector - Keyed K (Slate)
■ Flammability Rating	Low Smoke Zero Halogen (LSZH)
■ Pricing Description	LC (keyed K - slate) to LC (keyed K - slate) LSZH MM DPLX patch cord, 10 GbEm
■ Min. Order UOM	PC
■ Min. Order Qty.	1
■ BOM Qty. (# of Pkgs.)	0
■ Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.