

# PVM fast-acting 13/32" x 1-1/2" (10x38 mm) 600 Vdc photovoltaic fuses

RoHS



## Catalog symbol:

- PVM-(amp)

## Description:

A range of fast-acting UL 248-19 600 Vdc 13/32" x 1-1/2" (10x38 mm) fuses specifically designed to protect solar power systems in extreme ambient temperature, high cycling and low level fault current conditions (reverse current, multi-array fault).

## Specifications:

### Ratings

- Volts 600Vdc to UL 248-19
- Amps 4 - 30A
- IR 50 kA DC (4-30A)

### Electrical characteristics

Catalog number	Amp rating	Power loss (watts)	
		$0.8 \times I_n$	$1.0 \times I_n$
PVM-10	10	1.04	1.86
PVM-15	15	1.00	1.72
PVM-30	30	1.65	2.91


### Agency information

- UL® Listed, 248-19, Guide JFGA, File E335324
- CSA® Component Certified C22.2
- RoHS compliant

## Catalog numbers (amps)

PVM-4	PVM-7	PVM-10	PVM-20
PVM-5	PVM-8	PVM-12	PVM-25
PVM-6	PVM-9	PVM-15	PVM-30

## Dimensions:



## Typical applications:

- Combiner boxes
- Inverters
- Solar strings


## Recommended fuse blocks / holders:

Catalog symbol	Description	Doc no.
CHM	600 V DIN-Rail fuse holder	3185
CHPV	1000 V DIN-Rail fuse holder	3185
BPVM	1000 V modular blocks	10625
BMM	600 V modular blocks	10241
HEB	600 V In-Line fuse holder	2127
1A3400-__	PCB fuseclip	2131



Powering Business Worldwide

Time-current curves:



The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
Eaton.com  
  
Bussmann Division  
114 Old State Road  
Ellisville, MO 63021  
United States  
Eaton.com/bussmannseries

© 2017 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 2153 — BU-SB11985  
January 2017

Eaton and Bussmann are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

CSA is a registered trademark of the Canadian Standards Group.  
UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton’s Bussmann series  
product information,  
call **1-855-287-7626** or visit:  
**Eaton.com/bussmannseries**