




## TXR18AB00-1608BI Product Details

[!\[\]\(003082e50e3009141f59bd5df831749f\_img.jpg\) Share](#) [!\[\]\(f439ede8735757e3190eab35e168f1de\_img.jpg\) Print](#) [!\[\]\(f5c165e0bd35116675db6686a30b1fea\_img.jpg\) Email](#)**TXR18AB00-1608BI**

### Braid, Fixed, Spin and Tinel Lock Adapters

[Not EU RoHS or ELV Compliant](#)**Product Highlights:**

- Applies To Cable
- Style = Tinel Lock
- Connector Code = 18
- Straight
- Shell Size = 16, 16S

[View all Features](#)**Quick Links**

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 961189-000

 Active[!\[\]\(19d44b37fb4fa155bf9d60c77a3d3cb2\_img.jpg\) Add to My Part List](#)[!\[\]\(5a351309c3b87e4420622c1f0e57efc0\_img.jpg\) Request Sample](#)[!\[\]\(bff896c19919791b89ab521f039b410a\_img.jpg\) Find Similar Products](#)[!\[\]\(23a2e9ddc7bb0ef55393d38b772a848d\_img.jpg\) Buy Product](#)**Documentation & Additional Information****Product Drawings:**

- [Tinel-Lock Adapter](#) (PDF, English)

**Related Products:**

- [Tooling](#)

**Catalog Pages/Data Sheets:**

- None Available

**Product Specifications:**

- None Available

**Application Specifications:**

- None Available

**Instruction Sheets:**

- None Available

**CAD Files:**

- None Available

[List all Documents](#)**Product Features** (Please use the Product Drawing for all design activity)**Product Type Features:**

- [Style](#) = Tinel Lock
- [Angle](#) = Straight
- [Shell Size](#) = 16, 16S
- [Finish](#) = Cadmium Plating over Electroless Nickel
- [Material](#) = Aluminum Alloy
- [Color](#) = Olive Drab

**Configuration Features:**

- [Braid](#) = Double 36 AWG Braid, Single 30 AWG Braid
- [Material Code](#) = A

**Industry Standards:**

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

**Conditions for Usage:**

- [Applies To](#) = Cable

**Other:**

- [Brand](#) = Raychem

**Electrical Characteristics:**

- [Boot Diameter \(mm \[in\]\)](#) = 20.32 [0.800]
- [Entry Diameter \(mm \[in\]\)](#) = 12.70 [0.500]
- [Finish Code](#) = B

**Body Features:**

- [Connector Code](#) = 18
- [Entry Size](#) = 8
- [Cable Diameter \(Max.\) \(mm \[in\]\)](#) = 12.19 [0.480]

**Corporate Information**

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

**Quick Links**

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

**Customer Support**

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

**Keep Me Informed**

Receive TE News, Events &amp; Technology Updates

 Provide Website Feedback 