

# MODEL TL-2100



International size reference: AA, ER14505

## TECHNICAL DATA

(Typical values @+25°C for batteries stored for one year or less)



|                                          |                 |
|------------------------------------------|-----------------|
| ■ Nominal capacity @ 2 mA, to 2V         | 2.1 Ah          |
| ■ Rated voltage                          | 3.6 V           |
| ■ Maximum recommended continuous current | 120 mA          |
| ■ Maximum pulse current capability       | 200 mA          |
| ■ Weight                                 | 17.6g (0.62 oz) |
| ■ Volume                                 | 8 cc            |
| ■ Operating temperature range            | -55°C to +85°C  |
| ■ U.L. Component Recognition, MH 12193   |                 |

***TADIRAN  
LITHIUM  
BATTERIES***



### AVAILABLE TERMINATIONS

|                            |               |
|----------------------------|---------------|
| SUFFIX- /S STANDARD        | 15-5103-21500 |
| SUFFIX- /T SOLDER TABS     | 15-5103-31500 |
| SUFFIX- /P AXIAL PINS      | 15-5103-41500 |
| SUFFIX- /PT2 RADIAL PINS   | 15-5103-36500 |
| SUFFIX- /TP POLARIZED TABS | 15-5103-52500 |
| SUFFIX- /PT POLARIZED TABS | 15-5103-53500 |



***LITHIUM XTRA***

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

Rev. B 04/03