





[illegible]

UK plug



Eingangsdaten/ input data	:	100–240V AC $\pm 10\%$ / 50/60Hz 0.4A
Ausgangsdaten/ output data	:	15V DC $\pm 10\%$ 1000mA
Isolation/ insulation	:	4kV Eingang/Ausgang primary/secondary
Schutzart/ protection	:	IP 20
Approbation/ approval	:	CE; cULus; SAA; BEAB; GS
Gehäuse/ case	:	Steckergehäuse schwarz, Material UL94V0/ plug-in case black, material UL94V0
Betriebstemperatur/ operating temperature	:	0°C.....+25°C
Lagertemperatur/ storage temperature	:	-25°C.....+50°C
Gewicht/ weight	:	ca. xxxg inkl. Verpackung und Zubehör/ approx. xxxg incl. package and accessories
Verpackung/ packaging	:	Einzelverpackung, XXXXXmm (LxBxH) individual package, XXXXXmm (LxWxH)



flatcable black with white marking
length 1.8m $\pm 10\%$

Verwendungsbereich/Application range für Anfrage/for inquiry xxx/xx				Zul. Abweichung/ Allowable deviation		Oberfläche/ Surface		Maßstab/Scale 1:1		Gewicht/Weight	
								Werkstoff/Work material, Modell-Nr. XXXXXXXXXXXXXXXXXXXXXXXXXXXX			
				2008 Erstellt/ Drawn by		Datum/Date 15.01.		Name KK		Zeichnungsname/Drawing name Power supply ASN15HD+/AS10H+	