


CDS6U


8 mm

50 x 82 mm

10 mm

Polyamide 6.6

2 screw clamps



22-8 AWG

0.2-6 sq.mm

22-8 AWG

600 V

800 V

600 V

45 A


41 A

45 A

14 lb-in

0.8 Nm

14 lb-in


CDS6U/TS

NEW

8 mm

50 x 82 mm

10 mm

Polyamide 6.6

2 screw clamps



22-8 AWG

0.2-6 sq.mm

22-8 AWG

600 V

630 V

600 V

45 A


41 A

45 A

14 lb-in

0.8 Nm

14 lb-in


CDS6U/FT

NEW

6 mm

50 x 82 mm

10 mm

Polyamide 6.6

2 screw clamps



22-8 AWG

0.2-6 sq.mm

22-8 AWG

600 V

1000 V

600 V

45 A


41 A

45 A

14 lb-in

0.8 Nm

14 lb-in


CDS6U/SC

NEW

6 mm

50 x 82 mm

10 mm

Polyamide 6.6

2 screw clamps



22-8 AWG

0.2-6 sq.mm

22-8 AWG

600 V

800 V

600 V

45 A

41 A

45 A

14 lb-in

0.8 Nm

14 lb-in



Cat. No.	Std. Pk.
CDS6U	50
EPCDS6U	50



Cat. No.	Std. Pk.
CDS6U/TS	50
EPCDS6U	50



Cat. No.	Std. Pk.
CDS6U/FT	50
EPCDS6U	50



Cat. No.	Std. Pk.
CDS6U/SC	50
EPCDS6U	50



CA702	50
CA802	50
CA723/2	100
CA723/3	50
CA723/4	50
CA723/5	50
CA723/10	10
SLS2	50
SLS4	25
TPSLS	100
TPSLSR	100
TPSLSY	100
TPSLSBU	100
TPSLSBK	100
SWCDS	50
LCCDS	50
MT8	100

CA702	50
CA802	5
CA723/2	100
CA723/3	50
CA723/4	50
CA723/5	50
CA723/10	10
SLS2	50
SLS4	25
TPSLSR	100
TPSLSY	100
TPSLSBU	100
TPSLSBK	100
SWCDS	50
LCCDS	50
MT8	100

CA702	50
CA802	5
CA723/2	100
CA723/3	50
CA723/4	50
CA723/5	50
CA723/10	10
SLS2	50
SLS4	25
TPSLS	100
TPSLSR	100
TPSLSY	100
TPSLSBU	100
TPSLSBK	100
SWCDS	50
LCCDS	50
MT8	100

CA702	50
CA802	5
CA723/2	100
CA723/3	50
CA723/4	50
CA723/5	50
CA723/10	10
SLS2	50
SLS4	25
TPSLS	100
TPSLSR	100
TPSLSY	100
TPSLSBU	100
TPSLSBK	100
SWCDS	50
LCCDS	50
MT8	100