


**General ordering data**

Order No.	9510240000
Part designation	Klippon POK 5 Ex
Version	EXI enclosure, 91 mm, 120 mm, 220 mm, glass fibre-reinforced polyester
EAN	4008190498580
Qty.	1 pc(s).

Dimensions

Fixing dimension, height	82 mm
Fixing dimension, width	204 mm
Height	91 mm
Length	120 mm
Width	220 mm

General details

Cover fixing	4 stainless steel M6 screws
Enclosure fixing	Holes 6 mm
Sealing material	Polyurethane and chloroprene
Colour	grey
Class of protection to EN 60529	IP 66
Weight	1,060 g
Ambient temperature, min.	-40 °C
Ambient temperature, max.	90 °C

Screwed cable glands top/bottom

M 12	24
M 16	14
M 20	12
M 25	5
M 32	4
M 40	3
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M12	8
M16	4
M20	3
M25	1
M32	1
On housing side	left / right

Approvals

Approvals institutes

**Classifications**

ETIM 2.0	EC000520
ETIM 3.0	EC000049
eClass 4.1	27-14-12-06
eClass 5.0	27-18-05-02
eClass 5.1	27-18-05-02

Similar products

Order No.	Part designation	Version
1277600000	Klippon POK 5	Housings, 91 mm, 120 mm, 220 mm, glass fibre-reinforced polyester