

Sales Outline DrawingRevision **A****OBSOLETE- USE PK-21N30PQ****Specifica**

Resonant Frequency (Hz)	3000 $\pm$ 500
Operating Voltage (Vdc)	1.5 ~ 30
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	12 at Rated Voltage
Sound Pressure Level Min. (dB)	80 at 30cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 777D UL94HB plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	2.6
Options	For other options contact factory

Dimensions: (units: mm)