



FEATURES:

- SMD Grabber® Test Clip features gold plated stainless steel pincer for durability and low contact resistance.
- Ideal for jumping to .025" (.64mm) square pins.
- Receptacle is gold plated to optimize the electrical connection.

MATERIALS:

SMD GRABBER: Pincer, Stainless Steel, Gold Plated Spring, Stainless Steel

Insulation: Nylon 6, Color Matches Wire Color

Wire: 22 AWG, 26 x 36 t.c., PVC Insulation .064" (1.63mm) O.D. Nom.

Receptacle Body – Phosphor Bronze, Gold Plated

Housing: Polypropylene, Color Matches Wire

RATINGS:

Operating Voltage: 150 VRMS/DC

Operating Temperature: +50°C (+122°F)

Current: 0.5 Amperes Max.

ORDERING INFORMATION: Model 5412

Single Patch Cord:

5412-Length-Color Code

XX = Length in Inches, Standard Lengths: 12" (30.48cm), 24" (60.96cm), 36" (91.44cm)

* = Color, Standard Colors: -0 Black, -2 Red

Additional lengths can be quoted upon request.

ORDERING INFORMATION: Model 5924

Kit containing 10 pieces of Model 5412-12, one each of ten colors

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA