





PART NAME	NBF SERIES PLASTIC NEMA BOX			PART No.	NBF-32044 & NBF-32144 & NBF-32244 & NBF-32344 & NBF-32444			REVISION DATE	7/9/2010	
MATERIAL		FLAMMABILITY RATING	CONTINUOUS OPERATING TEMP.	FINISH: _____						
ABS		UL94-HB	-40°C ~ +60°C / -40°F ~ 140°F	BODY_____ LIGHT GRAY						
CLEAR PC		UL94-V0 UV STABILIZED	-40°C ~ +130°C / -40°F ~ 266°F	COVER_____ LIGHT GRAY OR CLEAR						
ABS / PC BLEND		UL94-5VA	-40°C ~ +85°C / -40°F ~ 185°F	LATCHES & HINGES_____ PLASTIC						
PBT / PC BLEND		UL94-5VA + UV (f1)	-40°C ~ +75°C / -40°F ~ 167°F	WALL MOUNTING BRACKETS__ STAINLESS STEEL & HARDWARE						


BODY



COVER



ASSEMBLY



NOTES:

- 1) UNIT COMES COMPLETE WITH
(4) WALL MOUNTING BRACKETS &
(4) M5 x 10mm LG. SELF-TAPPING SCREWS.
(NOT SHOWN)
- 2) BOXES DESIGNED TO MEET THESE STANDARDS:
NEMA 1,2,4,4X, AND IEC529-IP65 REQUIREMENTS.

TOLERANCE:

ALL DIMENSIONS HAVE $\pm 0.039\text{in}$ [$\pm 1\text{mm}$]
TOLERANCE UNLESS OTHERWISE SPECIFIED.

PART NO.	MATERIAL		USE
	BODY	COVER	
NBF-32044	ABS	ABS	INDOOR
NBF-32144	ABS / PC	ABS / PC	INDOOR
NBF-32244	ABS / PC	CLEAR PC	INDOOR
NBF-32344	PBT / PC	PBT / PC	OUTDOOR
NBF-32444	PBT / PC	CLEAR PC	OUTDOOR