


Wire Connector

Part No: HE3/600V

SYM.	CHANGES	BY	DATE



Working Temperature: 105° C

Wire Range: #22 - #14 AWG

Max: 4#16 w /1#20 Min: 1#18 x/1#20

Voltage: 600V

Voltage for fixtures and signs: 1000V

All dimensions in mm unless otherwise stated: 0. = ±0.1mm 00. = ±0.2mm 000. = ±0.2mm

NO.	1	2			3
NAME	MATERIAL	COLOR			INTERNATIONAL APPROVALS: UL/CSA: # E34181
MAT'L.	UL 94V-2 FLAME-RETARDANT	ORANGE			
REMARK	THERMOPLASTIC				
APPROVED BY:		CHECKED BY:		DRAWN BY:	



HOFFMAN PRODUCTS

20700 Hubbell Avenue, Oak Park, MI 48237

Tel: 1-800-645-2014 • Fax: 1-800-908-1295

Web: www.hoffmanproducts.com

DATE:	TITLE: Wire Connector		
SCALE: FREE	PART NO. HE3/600V		
DRAWING NO. H90509	PART NAME	ISSUE	