

MINIATURE LAMP (1864) Details



Part #	1864				
Description	T3 1/4 M BAY 28V .17A 3CP				
Bulb Shape	T-3 1/4	Filament	C-2F	Base Style	Miniature Bayonet (BA9s)
Glass Diameter (in)	0.39	MOL [†] (in)	1.19	LCL ^{††} (in)	0.63
Glass Diameter (mm)	10	MOL (mm)	30.20	LCL (mm)	16.00
Volts	28	MSCP [‡]	3	Avg Life Hrs	1500
Watts	4.76	Amps	0.17	RoHS Compliant	

† MOL (Maximum Overall Length):
The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):
Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):
The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.