

D-SUB pressure nut - VS-M16 (5-9) - 1688447

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



D-SUB cap nut with line seal, for sleeve housing VS-09-..., conductor diameter of 5 mm ... 9 mm



Key commercial data

Packing unit	1
Minimum order quantity	5
Catalog page	Page 441 (PC-2011)
GTIN	 4 017918 818364
Custom tariff number	85472000
Country of origin	GERMANY

Technical data

Mechanical characteristics

External cable diameter	5 mm ... 9 mm
Color	gray
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (assembly)	-20 °C ... 80 °C

Material data

Inflammability class according to UL 94	V0
Housing material	PA
Sealing material	Neoprene
Seal material	Neoprene
Degree of protection	IP67

Classifications

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441

D-SUB pressure nut - VS-M16 (5-9) - 1688447

Classifications

ETIM

ETIM 4.0	EC000441
ETIM 5.0	EC002355

UNSPSC

UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522
UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109

Drawings

Dimensioned
drawing

D-
SUB
cap
nut