

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

46818-0001

Status:

Active

Description:

EXTreme Guardian™ Crimp Harness Housing, 3 Circuit, 11.00mm Pitch, 8 -10 AWG

Documents:

3D Model

Drawing (PDF)

Product Specification PS-46819-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

TUV

UL

R72130381

E29179

General

Product Family

Series

Application

Product Name

UPC

Crimp Housings

46818

Wire-to-Board, Wire-to-Wire

EXTreme Guardian™

883906730963

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Keying to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Temperature Range - Operating

3

Black

94V-0

Male

No

None

Polyester

15.840/g

1

Bag

No

11.00mm

-40°C to +105°C

Electrical

Current - Maximum per Contact

80A

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-46819-001

SD-46818-001



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

46818Series

Mates With

46817 EXTreme Guardian™ 3 Circuit Power Plug Assembly

Use With

46819 High Power Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION