


Dimensions:mm (In.)



Electrical Specifications:

- Rating: 50mA/12VDC
- Contact resistance: 100m Ω max.
- Insulation resistance: 100M Ω min. @ 500VDC
- Dielectric strength: 250VAC for 1 minute
- Life: 500,000 cycles

Mechanical Specifications:

- Type: SPST
- Operating force: 160 \pm 50gf
- Stroke: .35mm +.2mm -.1mm
- Operating temperature: -25 $^{\circ}$ ~+70 $^{\circ}$ C

Material:

- Button color: brown

Note:

- RoHS Compliant and are also process compatible with 260 $^{\circ}$ solder

Tactile Switch (Thru-Hole)
101-0621-EV



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0621-EV](#)