







PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxP81C5A40LF	40	200	without	without
D*LxWxP81C5A40LF	40	200	insert M3	without
D*OxWxP81C5A40LF	40	200	insert UNC 4.40	without
D*VxWxP81C5A40LF	40	200	female screw UNC 4.40	without
D*xWxP81C5M40LF	40	200	without	metal bracket
D*LxWxP81C5M40LF	40	200	insert M3	metal bracket
D*OxWxP81C5M40LF	40	200	insert UNC 4.40	metal bracket
D*VxWxP81C5M40LF	40	200	female screw UNC 4.40	metal bracket

shell size
*
E
A
A
B
C

LAYOUTS
xWx
2V2
3V3
3W3
5W5
8W8




PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxP81C6A40LF	40	500	without	without
D*LxWxP81C6A40LF	40	500	insert M3	without
D*OxWxP81C6A40LF	40	500	insert UNC 4.40	without
D*VxWxP81C6A40LF	40	500	female screw UNC 4.40	without
D*xWxP81C6M40LF	40	500	without	metal bracket
D*LxWxP81C6M40LF	40	500	insert M3	metal bracket
D*OxWxP81C6M40LF	40	500	insert UNC 4.40	metal bracket
D*VxWxP81C6M40LF	40	500	female screw UNC 4.40	metal bracket









Copyright FCI.

www.fciconnect.com		surface ISO 1302	-	tolerance std ISO 406 ISO 1101	projection mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	M PESSON	11/10/05	ANGULAR	0.X ±0.3	size A2
Eng	11/10/05	P LEGARE	LINEAR	0.XX ±0.1	Scale 2:1
Chr			0° ±2°	0.XXX ±0.05	ECN LS07-0273
Appr			Product family	-	Spec ref
FCI		SUB MALE DW EUROPE foot print			Rev. C
		full power right angle press fit			
		catalog no	-	YY	sheet 3 of 5

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table 1 sheet 1



LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table 1 sheet 1



SIDE VIEW FOR ALL LAYOUTS

