


RP73D2B619RBTG Product Details

[Share](#) |
 [Print](#) |
 [Email](#)



RP73D2B619RBTG
(1-1879258-6)

TE Internal Number: 1-1879258-6

[Active](#)

Fixed Resistors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Fixed Resistor
- Resistor Type = Precision Resistor
- Resistance Selection = <1K Ω
- Resistance = 619 Ω
- Power Rating = .25 W

[View all Features](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • 1309350 PASSIVE COMPONENT (PDF, English) • SMD Precision Resistors - Type RP73 Series - Tyco El... (PDF, English) • 8-1773459-4 POWER FILTERING AND RESISTIVE SOLUTIONS ... (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Fixed Resistor • Resistor Type = Precision Resistor • Element = Thin Film • Series = RP73 • Termination Type = Solder <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Resistance Selection (Ω) = <1K • Resistance (Ω) = 619 • Power Rating (W) = 0.25 • Tolerance (%) = 0.1 • Package Type = Cut Tape Length <p>Body Features:</p> <ul style="list-style-type: none"> • Mount Style = Surface Mount • Packaging Style = 1206 • Package, Component Size = 3.2x 1.6 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Number of Terminations = 2 • Number of Resistors = 1 <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C • RoHS/ELV Compliance History = Always was RoHS compliant <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Temperature Coefficient (ppm/°C) = ± 15 <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = Precision <p>Other:</p> <ul style="list-style-type: none"> • Brand = Holsworthy

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

