






Y-type powersinks

A compact design for moderate power involvement, particularly on PC boards.





Code	Length		Thermal rating θ °C/watt
	ins	mm	
2Y	2	50.8	6.2
3Y	3	76.2	4.8
3.5Y	3.5	89.0	4.2
4Y	4	101.6	3.9
6Y	6	152.4	2.8



Thermal performance with one device centrally mounted, using Thermpath 167, fins vertical, convection air. Finish Black.




Stock hole variants (Y-1 has no holes)



GY-Type powersinks

Grooved for TO-220 devices



Extruded slots accept Cover-slides
(see data sheet) to shield devices.