


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO	NOMINAL I.D.	BUNDLE DIA.	NO. OF CARRIERS	NO. OF STRANDS PER CARRIER	WEIGHT /1000 ft lbs (kg)
SE12PSC-TRO	0.125 (3.18)	0.125 - 0.250 (3.18 - 6.35)	32	3	3.96 (1.8)
SE25PSC-TRO	0.250 (6.35)	0.156 - 0.438 (3.96 - 11.12)	40	3	4.64 (2.10)
SE38PSC-TRO	0.375 (9.53)	0.188 - 0.625 (4.77 - 15.88)	56	3	7.44 (3.37)
SE50PSC-CRO	0.500 (12.70)	0.250 - 0.750 (6.35 - 19.05)	64	3	8.22 (3.73)
SE75PSC-CRO	0.750 (19.05)	0.625 - 1.00 (15.88 - 25.40)	80	3	11.13 (5.05)
SE125PSC-LRO	1.250 (31.75)	1.0 - 1.50 (25.40 - 38.10)	120	3	15.55 (7.05)
SE150PSC-LRO	1.500 (38.10)	1.25 - 2.00 (31.75 - 50.8)	120	4	18.50 (8.40)

SE 12 PSC - T R O

COLOR 0 : WEATHER RESISTANT BLACK

REEL

PACKAGE SIZE L = 50 FT (15.24 M)
C = 100 FT (30.48 M)
T = 200 FT (60.96 M)
D = 500 FT (152.4 M)
M = 1000 FT (304.8 M)

MATERIAL PSC : SCISSOR CUT (FRAY RESISTANT) PET

NOM. I.D. SIZE 12 = 0.125 (3.2)
25 = 0.250 (6.4)
38 = 0.375 (9.5)
50 = 0.500 (12.7)
75 = 0.750 (19.1)
125 = 1.250 (31.8)
150 = 1.500 (38.1)

SLEEVING EXPANDABLE

NOTES:

1. ALL STRANDS OF THE PET SLEEVING SHALL BE THE SAME COLOR.

2. REELS MAY HAVE SPLICES, DEPENDING ON LENGTH:

LENGTH	50 FT	100 FT	200 FT	500 FT	1000 FT
MAX SPLICES	0	1	1	2	3

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03597BX_DC_GB0239LX_00/00B

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

FRAY RESISTANT SLEEVING (SE__PSC-__)
(CUSTOMER DRAWING)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± "N/A" (.XXX) ± "N/A"
(.XX) ± "N/A" ANGLES ± "N/A"

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE
PROJECTION.

DRAWN BY

JAD

MAT'L:

DATE

8/23/06

SEE TABLE

CHK'D

SCALE

N/A

DRAWING NO.

GB0239LX

DWG

A

SIZE

00B	3/26/12	LEF	VJS	A: ADD NOTE #2 AND TABLE B: MAKE ALL TOLERANCES "N/A" C: ADD CUSTOMER DRAWING TO DESCRIPTION	GB0239LX	00B	RAMI		
R	8/23/06	JAD		INITIAL RELEASE	GB0239LX	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	