


Visit Mallory's Website at www.nacc-mallory.com



CGS Computer Grade Capacitors

High performance computer grade capacitor. Long life expectancy available in high or low post configurations. **Operating Temperature:** -40°C to + 85°C. Low ESR high ripple capabilities. **Voltage Range:** 6.3 WVDC 500 WVDC. **Tolerance:** -10% +75% up to 150 WVDC, -10% +50%, 200-450 WVDC.

Stock No.	Mfr.'s Type	WV DC	MFD	Case Size (In.) Dia. x L	EACH		
					1-24	25-49	50-99
857-0201	CGS183U010R2C	10	18000	1 1/8 x 2 1/8	9.60	8.78	8.08
857-0051	CGS153U016R2L	16	15000	1 1/8 x 2 1/8	9.63	8.74	7.99
857-0052	CGS173U016R3C	16	17000	1 1/8 x 3 1/8	8.75	8.01	7.36
857-0200	CGS243U016R3C	16	24000	1 1/8 x 3 1/8	9.14	8.24	7.64
857-0054	CGS253U016V2C	16	25000	2 x 2 1/8	11.50	9.32	8.86
857-0055	CGS343U016R4C	16	34000	1 1/8 x 4 1/8	12.11	10.99	10.05
857-0056	CGS383U016V3C	16	38000	2 x 3 1/8	12.45	11.42	10.44
857-0216	CGS553U016V3L	16	55000	2 x 3 1/8	14.20	13.02	11.90
857-0202	CGS663U016X3C	16	66000	2 x 4 1/8	18.09	16.32	14.86
857-0204	CGS104U016X5C	16	100000	3 x 5 1/8	33.97	30.64	28.41
857-0060	CGS114U016W4C	16	110000	2 1/2 x 4 1/8	23.53	21.58	19.91
857-0206	CGS124U016X3L	16	120000	2 x 3 3/8	29.11	26.26	24.35
857-0224	CGS214U016X5R	16	210000	3 x 5 1/8	38.94	35.70	32.95
857-0006	CGS562U025R3C	25	5600	1 1/8 x 3 1/8	9.33	8.46	7.73
857-0007	CGS892U025R3C	25	8900	1 1/8 x 3 1/8	11.00	9.98	9.12
857-0208	CGS103U025R3C	25	10000	1 1/8 x 3 1/8	8.29	7.48	6.94
857-0008	CGS123U025V3C	25	12000	2 x 3 1/8	11.67	10.59	9.69
857-0038	CGS183U025R4C	25	18000	1 1/8 x 4 1/8	13.02	11.82	10.80
857-0065	CGS283U025V3C	25	28000	2 x 3 1/8	14.20	13.02	11.89
857-0046	CGS293U025V4C	25	29000	2 x 4 1/8	18.16	16.55	15.22
857-0125	CGS473U025V4C	25	47000	2 x 4 1/8	16.82	15.42	14.09
857-0236	CGS653U025W4C	25	65000	2 1/2 x 4 1/8	22.98	21.07	19.25
857-1075	CGS124U025X4C	25	120000	3 x 4 1/8	34.64	31.76	29.27
857-0210	CGS452U030R2C	30	4500	1 1/8 x 2 1/8	8.05	7.26	6.73
857-0127	CGS802U030R3C	30	8000	1 1/8 x 3 1/8	8.90	8.09	7.39
857-0072	CGS303U030V4C	30	30000	2 x 4 1/8	15.74	14.43	13.18
857-0212	CGS553U030W4C	30	55000	2 1/2 x 4 1/8	24.44	22.04	20.44
857-0129	CGS104U030X5L	30	100000	3 x 5 1/8	39.72	36.77	33.95
857-0274	CGS123U035R4C	35	12000	1 1/8 x 4 1/8	10.11	9.19	8.40
857-0280	CGS703U035X4C	35	70000	3 x 4 1/8	34.38	31.52	29.09
857-0012	CGS222U040R2C	40	2200	1 1/8 x 2 1/8	7.82	7.09	6.49
857-0047	CGS272U040R2C	40	2700	1 1/8 x 2 1/8	7.76	7.04	6.44
857-0080	CGS352U040R2C	40	3500	1 1/8 x 2 1/8	7.97	7.22	6.60
857-0013	CGS422U040R3C	40	4200	1 1/8 x 3 1/8	9.50	8.62	7.88
857-0124	CGS472U040R2C	40	4700	1 1/8 x 2 1/8	11.88	10.79	9.85
857-0014	CGS512U040R3C	40	5100	1 1/8 x 3 1/8	8.19	7.43	6.80
857-0073	CGS602U040R3C	40	6000	1 1/8 x 3 1/8	9.31	8.45	7.72
857-0130	CGS902U040R4C	40	9000	1 1/8 x 4 1/8	10.26	9.31	8.51
857-0015	CGS113U040V3C	40	11000	2 x 3 1/8	12.11	10.99	10.05
857-0214	CGS123U040R4C	40	12000	1 1/8 x 4 1/8	10.31	9.30	8.62
857-0077	CGS133U040V4C	40	13000	2 x 4 1/8	14.30	12.63	11.57
857-0016	CGS173U040V4C	40	17000	2 x 4 1/8	13.77	12.62	11.54
857-0009	CGS173U040V3C	40	17000	2 x 3 1/8	14.95	13.58	10.56
857-0218	CGS203U040V5L	40	20000	2 x 5 1/8	16.94	17.08	15.84
857-0131	CGS223U040V3C	40	22000	2 x 3 1/8	19.25	17.65	16.14
857-0220	CGS233U040V4C	40	23000	2 x 4 1/8	14.79	13.34	12.37
857-1079	CGS333U040V4C	40	33000	2 x 4 1/8	21.47	20.02	18.17
857-0036	CGS403U040W4C	40	40000	2 1/2 x 4 1/8	22.84	20.93	19.13
857-0222	CGS683U040X4C	40	68000	3 x 4 1/8	35.99	32.46	30.10
857-0081	CGS162U050R2C	50	1600	1 1/8 x 2 1/8	7.75	7.05	6.43
857-0017	CGS222U050R2C	50	2200	1 1/8 x 2 1/8	7.57	6.86	6.28
857-0063	CGS292U050R3C	50	2900	1 1/8 x 3 1/8	9.06	8.22	7.52
857-0018	CGS412U050R3C	50	4100	1 1/8 x 3 1/8	9.34	8.48	7.75
857-0084	CGS492U050R3L	50	4900	1 1/8 x 3 1/8	10.18	9.24	8.44
857-0134	CGS502U050R3C	50	5000	1 1/8 x 3 1/8	9.72	8.83	8.07
857-0228	CGS612U050R4C	50	6100	1 1/8 x 4 1/8	9.80	8.84	8.20
857-0086	CGS652U050V3C	50	6500	2 x 3 1/8	11.55	10.48	9.56
857-0284	CGS682U050R3C	50	6800	1 1/8 x 3 1/8	10.25	9.31	8.51
857-0021	CGS962U050V4C	50	9600	2 x 4 1/8	19.56	17.93	16.38
857-0136	CGS103U050R4C	50	10000	1 1/8 x 4 1/8	11.51	10.46	9.53
857-0137	CGS133U050V3C	50	13000	2 x 3 1/8	14.41	13.21	12.06
857-0088	CGS153U050V4C	50	15000	2 x 4 1/8	14.71	13.47	12.32
857-0499	CGS183U050V3C	50	18000	2 x 3 1/8	16.08	14.74	13.46
857-0139	CGS203U050V4C	50	20000	2 x 4 1/8	17.01	15.60	14.26
857-0040	CGS243U050W3C	50	24000	2 1/2 x 3 1/8	30.41	27.88	25.74
857-0140	CGS253U050W4C	50	25000	2 1/2 x 4 1/8	21.43	19.65	17.96
857-0044	CGS273U050V4C	50	27000	2 x 4 1/8	22.73	20.83	19.03

Stock No.	Mfr.'s Type	WV DC	MFD	Case Size (In.) Dia. x L	EACH		
					1-24	25-49	50-99
857-0230	CGS313U050W4C	50	31000	2 1/2 x 4 1/8	25.06	22.60	20.96
857-0232	CGS433U050X5C	50	43000	3 x 5 1/8	43.28	39.04	36.19
857-0288	CGS483U050X4C	50	48000	3 x 4 1/8	38.67	35.44	32.71
857-0290	CGS603U050X5C	50	60000	3 x 5 1/8	40.37	37.02	34.17
857-0292	CGS104U050X8L	50	100000	3 x 8 1/8	68.77	63.04	58.18
857-0089	CGS152U075R3C	75	1500	1 1/8 x 3 1/8	9.61	8.74	7.97
857-0234	CGS222U075R2C	75	2200	1 1/8 x 2 1/8	8.47	7.64	7.08
857-0091	CGS292U075R3C	75	2900	1 1/8 x 3 1/8	9.46	8.59	7.85
857-0092	CGS422U075R4C	75	4200	1 1/8 x 4 1/8	9.61	8.71	7.97
857-0023	CGS482U075V3C	75	4800	2 x 3 1/8	12.93	11.85	10.82
857-0238	CGS562U075R4C	75	5600	1 1/8 x 4 1/8	12.01	10.60	9.83
857-0240	CGS632U075R5L	75	6300	1 1/8 x 5 1/8	12.33	10.88	10.09
857-0142	CGS103U075V3C	75	10000	2 x 3 1/8	16.11	14.77	13.49
857-0143	CGS103U075V4C	75	10000	2 x 4 1/8	16.58	15.20	13.88
857-0169	CGS123U075V4C	75	12000	2 x 4 1/8	19.44	17.82	16.30
857-0294	CGS153U075V5L	75	15000	2 x 5 1/8	21.93	20.11	18.38
857-0296	CGS253U075W5L	75	25000	2 1/2 x 5 1/8	27.82	25.50	23.54
857-0487	CGS253U075X4C	75	25000	3 x 4 1/8	31.56	28.95	26.70
857-0144	CGS373U075X5L	75	37000	3 x 5 1/8	38.95	35.71	32.96
857-0022	CGS122U100R3C	100	1200	1 1/8 x 3 1/8	8.39	7.62	6.47
857-0498	CGS172U100R3C	100	1700	1 1/8 x 3 1/8	9.90	8.99	8.21
857-0024	CGS402U100V4C	100	4000	2 x 4 1/8	15.17	13.91	12.70
857-0252	CGS902U100V5L	100	9000	2 x 5 1/8	20.07	18.39	16.80
857-0145	CGS103U100W4C	100	10000	2 1/2 x 4 1/8	21.35	19.57	17.89
857-1069	CGS153U100W5L	100	15000	2 1/2 x 5 1/8	38.59	35.38	32.66
857-0254	CGS153U100X4C	100	15000	3 x 4 1/8	31.10	28.51	26.32
857-0098	CGS401U150R2C	150	400	1 1/8 x 2 1/8	8.62	7.82	7.15
857-0242	CGS112U150R4C	150	1100	1 1/8 x 4 1/8	10.51	9.46	8.79
857-0100	CGS352U150V5L	150	3500	2 x 5 1/8	19.09	17.50	15.98
857-0101	CGS572U150X4C	150	5700	3 x 4 1/8	32.42	29.72	27.43
857-0146	CGS872U150X5R	150	8700	3 x 5 1/8	40.00	36.65	33.83
857-0102	CGS591T200R3C	200	590	1 1/8 x 3 1/8	10.25	9.31	8.51
857-0103	CGS102T200R4C	200	1000	1 1/8 x 4 1/8	12.18	11.17	10.20
857-0244	CGS202T200V4C	200	2000	2 x 4 1/8	18.98	17.12	15.87
857-0011	CGS222T200V4C	200	2200	1 1/8 x 4 1/8	24.58	22.54	20.60
857-0148	CGS272T200V4C	200	2700	2 x 4 1/8	22.25	20.40	18.65
857-0298	CGS462T200X4C	200	4600	3 x 4 1/8	37.52	34.39	31.74
857-0300	CGS502T200W5C	200	5000	2 1/2 x 5 1/8	55.85	51.19	47.26
857-0304	CGS772T200X5L	200	7700	3 x 5 1/8	46.94	43.03	39.72
857-0042	CGS201T250R2C	250	200	1 1/8 x 2 1/8	8.32	7.55	6.90
857-0306	CGS251T250R2C	250	250	1 1/8 x 2 1/8	9.50	8.62	7.88
857-0246	CGS471T250R3C	250	470	1 1/8 x 3 1/8	9.14	8.24	7.64
857-0028	CGS551T250R4C	250	550	1 1/8 x 4 1/8	11.28	10.23	9.35
857-0030	CGS122T250V3C	250	1200	2 x 3 1/8	16.07	14.74	13.45
857-0308	CGS422T250W5L	250	4200	2 1/2 x 5 1/8	43.47	39.83	36.78
857-0150	CGS602T250X5L	250	6000	3 x 5 1/8	56.53	51.82	47.83
857-1076	CGS103T250X5L	250	10000	3 x 5 1/8	73.61	67.47	62.28
857-0071	CGS602T300X8L	300	6000	3 x 8 1/8	72.14	66.13	61.04
857-0152	CGS251T350R3C	350	250	1 1/8 x 3 1/8	9.82	8.91	8.14
857-0106	CGS381T350R4C	350	380	1 1/8 x 4 1/8	11.67	10.70	9.78
857-0310	CGS651T350V3C	350	650	2 x 3 1/8	20.25	18.57	16.97
857-0153	CGS102T350V4C	350	1000	2 x 4 1/8	20.20	17.82	16.32
857-0248	CGS132T350V5L	350	1300	2 x 5 1/8	25.32	22.84	21.18
857-0250	CGS222T350W5L	350	2200	2 1/2 x 5 1/8	46.83	42.24	39.17
857-0156	CGS332T350X5L	350	3300	3 x 5 1/8	51.22	46.95	43.35
857-0312	CGS750T450R2C	450	75	1 1/8 x 2 1/8	8.43	7.67	7.00
857-0107	CGS101T450R2C	450	100	1 1/8 x 2 1/8	8.80	7.98	7.30
857-0157	CGS141T450R3C	450	140	1 1/8 x 3 1/8	11.79	10.78	9.90
857-0256	CGS171T450R3C	450	170	1 1/8 x 3 1/8	11.24	10.14	9.40
857-0280	CGS211T450R4C	450	210	1 1/8 x 4 1/8	13.04	11.96	10.93
857-0254	CGS212T450V3C	450	210	1 1/8 x 4 1/8	12.10	11.00	10.06
857-0161	CGS321T450V3C	450	320	2 x 3 1/8	16.43	15.06	13.76
857-0161	CGS451T450V3C	450	450	2 x 3 1/8	20.21	18.53	16.93
857-0162	CGS651T450V4C	450	650	2 x 4 1/8	25.31	23.40	21.42
857-0262	CGS801T450V4L	450	800	2 x 4 1/8	27.96	25.64	23.66
857-0264	CGS102T450W4C	450	1000	2 1/2 x 4 1/8	32.49	29.77	27.50
857-0266	CGS142T450W5C	450	1400	2 1/2 x 5 1/8	42.07	37.86	34.42
857-0270	CGS192T450X4C	450	1500	3 x 4 1/8	48.91	44.02	40.06
857-0164	CGS164X5C	450	1600	3 x 5 1/8	54.23	49.06	45.02
857-0166	CGS182T450X5R	450	1800	3 x 5 1/8	55.53	46.33	42.75
857-0278	CGS192T450X5L	450	1900	3 x 5 1/8	56.67	50.00	46.36
857-0268	CGS202T450X5C	450	2000	3 x 5 1/8	56.60	51.88	48.06
857-0165	CGS242T450X5L	450	2400	3 x 5 1/8	59.90	54.91	50.69
857-0486	CGS332T450X5L	450	3300	3 x 5 1/8	111.96	102.63	94.73
857-0286	CGS332T450X8L	450	3300	3 x 8 1/8	115.49	103.94	94.49