




F6025 Series



Size: (60 x 60 x 25 mm)

2.36 x 2.36 x 0.98 inches

- Broad range of models to meet air flow and sound noise targets
- Electronic locked rotor sensor, auto-restart, reverse polarity protection
- 5, 12, or 24 VDC
- Ribbed or flanged frame styles; ball bearings
- Options include tachometer or locked rotor output signal, and thermistor control



Model No.	Rated Voltage (V)	Current (mA)			Revolution (RPM)	Air Volume (CFM)	Maximum Static Pressure (in H ₂ O)	Sound Noise (dBA)	Weight (oz)
		5	12	24					
F6025 S	5/12/24	150	75	40	2,300	12	0.07	22	2.47
F6025 L	5/12/24	190	85	45	2,800	14	0.09	24	2.47
F6025 M	5/12/24	270	95	55	3,300	17	0.13	27	2.47
F6025 H	5/12/24	410	140	80	3,800	20	0.16	31	2.47
F6025 E	5/12/24	700	230	125	4,600	24	0.23	36	2.47
F6025 X	12/24	—	330	170	5,200	27	0.28	41	2.47