


Mini-Din Plugs

171-2609


KOBI CONN

Mini-Din Plugs



Dimensions: mm (in.)

SPECIFICATIONS	
Voltage Rating:	100VAC 1A max.
Insulation Resistance:	50MΩ @ 500VDC
Dielectric:	500VAC for 1 minute
Contact Resistance:	30m Ω max.
Maximum Acceptable Wire Size:	16AWG
Boot:	PVC
Housing:	ABS
Shell:	Nickel plated brass
Insulator:	Polycarbonate
Pins:	Silver plated brass
Assembly:	Yes



ASSEMBLY SPECIFICATIONS		
1	Cover:	PVC black
2	Con:	A.B.S.
3	Shell:	Brass, nickel plated

Date Last Revised: 10-26-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 301078

171-2609

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-2609](#)