

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [90835-0057](#)
Status: **Active**
Overview: [RAST 5 Connector System](#)
Description: 5.00mm Pitch Appli-Mate RAST 5 IDT Connector System Female Receptacle, 16A, 2 Circuit, Natural, Coding Keys 01c, d20, Latch Position 1/2, Position Coding 1a,

Documents:

[3D Model](#) [Packaging Specification PK-90833-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family IDT and Solder Connectors
 Series [90835](#)
 Comments Female Indirect Receptacle Reference K12
 Crimp Quality Equipment Yes
 Overview [RAST 5 Connector System](#)
 Product Name RAST 5
 UPC 800754881548
 Use With RAST standard interface

Physical

Circuits (Loaded) 2
 Circuits (maximum) 2
 Color - Resin Natural
 Durability (mating cycles max) 10
 Flammability 94V-2
 Gender Female
 Glow-Wire Compliant No
 Lock to Mating Part Yes
 Material - Metal Phosphor Bronze
 Material - Plating Mating Silver
 Material - Plating Termination Silver
 Material - Resin Nylon
 Net Weight 3.035/g
 Number of Rows 1
 Packaging Type Tray
 Panel Mount No
 Pitch - Mating Interface 5.00mm
 Pitch - Termination Interface 5.00mm
 Plating min - Mating 2.032µm
 Plating min - Termination 0.102µm
 Polarized to Mating Part Yes
 Stackable Yes
 Temperature Range - Operating -20C to +120C
 Termination Interface: Style IDT or Pierce
 Wire Size AWG 16 Stranded, 18

Electrical

Current - Maximum per Contact 16A
 Voltage - Maximum 250V AC

Material Info



Series

image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[90835Series](#)

Mates With

[90858 Header](#), [90879 Header](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
RAST 5.0 Power Semi-Automatic Terminator Machine for 12 and 16 AMP	0623006100

Reference - Drawing Numbers

Packaging Specification
Sales Drawing

PK-90833-001
SD-90835-001

This document was generated on 06/30/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[90835-0057](#)