



1040

Micro

From small sensitive components to smartphones, protect your gear from the elements in a crushproof, watertight, & dustproof Micro Case from Pelican.

- ***Case is able to be submerged under 1 meter of water for up to 30 minutes in accordance with IP67 testing parameters**
- **Available in clear with color liner or solid**
- **Watertight, crushproof, and dustproof**
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- Carabiner
- Easy open latch
- Lifetime Guarantee of Excellence
- Rubber liner for extra protection doubles as o-ring seal
- Stainless steel hardware



DIMENSIONS

Interior (LxWxD)	6.50 x 3.87" x 1.75 (16.5 x 9.8 x 4.4 cm)
Exterior (LxWxD)	7.50 x 5.06" x 2.12 (19.1 x 12.9 x 5.4 cm)
Lid Depth	0.69" (1.8 cm)
Bottom Depth	0.94" (2.4 cm)
Total Depth	1.63" (4.1 cm)
Int Volume	0.03 ft ³ (0.001 m ³)

MATERIALS

Body	Polycarbonate (PC)
Latch	Xylex
O-Ring	Thermoplastic Rubber
Pins	Stainless Steel
Foam	TL - 426 4 lb. Esther
Purge Body	Polycarbonate (PC)
Purge Vent	Polyester Spun-Bond ePTFE Oleophobic

COLOURS

 Black	 Blue	 Red	 Yellow
 Black - Clear	 Yellow - Clear	 Blue - Clear	 Red - Clear

WEIGHT

Weight With Foam	0.71 lbs (0.3 kg)
Weight Empty	0.70 lbs (0.3 kg)
Buoyancy	1.26 lbs (0.6 kg)
Master Pack Weight	4.85 lbs (2.2 kg)

TEMPERATURE

Minimum Temperature	-10°F (-23.3 °C)
Maximum Temperature	199°F (92.8 °C)

CERTIFICATIONS

IP67

FOAM PROPERTIES

Layer 1 (Lid)	0.13" Pad
Layer 2 (Base)	0.91" Pick N Pluck

OTHER

Minimum Pack	6
Master Pack	6
Military	yes

ACCESSORIES



1041
Replacement Case Liner



1042
Pick N Pluck™ Foam Insert

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

Document created on 08-22-20