





Mating Part Number		
3220-ALL	3210-XX-001-11-XX	3210-XX-001-12-XX
3210-XX-002-12-XX	3210-XX-003-12-XX	



Specifications:
Current rating:1.0A AC,DC
Voltage rating:50V AC, DC
Contact testistance:20m ohm Max
Insulation resistance:1000M ohm Min
Withstanding voltage:500V AC/minute
Operating Temperature:-40°C ~ +105°C

Materials:
Insulator:PBT UL94V-0
Standard Color:Black
Terminal:Phosphor Bronze
Finish:Gold Plated

Dimension:

Pin.No	Dim.A	Dim.B	Pin.No	Dim.A	Dim.B
6	2.54	8.00	28	16.51	21.97
8	3.81	9.27	30	17.78	23.24
10	5.08	10.54	34	20.32	25.78
12	6.35	11.81	40	24.13	29.59
14	7.62	13.08	44	26.67	32.13
16	8.89	14.35	50	30.48	35.94
18	10.16	15.62			
20	11.43	16.89			
24	13.97	19.43			
26	15.24	20.70			

RoHS Compliant