

ISL9519

Narrow VDC Regulator/Charger with SMBus Interface

FN6773
Rev 3.00
March 1, 2012

The ISL9519 is a highly integrated Narrow VDC system voltage regulator and battery charger controller. Operating parameters are programmable over the System Management Bus (SMBus). The ISL9519 is designed for applications where the system power source is either the battery pack or the output of the regulator/charger. This makes the max voltage to the system equal to the max battery voltage instead of the max adapter voltage. The ISL9519 also includes a patented system to control trickle charging deeply discharged batteries while maintaining system voltage at a user defined minimum. High efficiency is achieved with a DC/DC synchronous-rectifier buck converter, equipped with diode emulation and variable switching frequency for enhanced light load efficiency and AC-adapter boosting prevention. The ISL9519 can charge one, two or three series connected Lithium-ion cells, at up to 8A charge current. Default settings for 1-, 2- or 3-cell operation at power-up are selected by an external pin. Integrated MOSFET drivers and bootstrap diode result in fewer components and smaller implementation area. Low offset current-sense amplifiers provide high accuracy.

The ISL9519 provides an open drain digital output that indicates the presence of the AC-adapter. The ISL9519 also provides an analog output that indicates the adapter current.

Related Literature

- See [AN1562](#), "ISL9519EVAL1Z Evaluation Board Setup Procedure" for applications with adapter voltage > 7V
- See [AN1570](#), "ISL9519EVAL2Z Evaluation Board Setup Procedure" for applications with adapter voltage > 5V

Features

- $\pm 0.5\%$ System Voltage Accuracy (-10°C to $+100^{\circ}\text{C}$)
- $\pm 3\%$ Accurate Input Current Limit (-10°C to $+100^{\circ}\text{C}$)
- $\pm 3\%$ Accurate Battery Charge Current Limit
- Variable Switching Frequency at Light Load Conditions for Higher Efficiency
- Fixed Frequency Operation at Higher Loads
 - Fixed Frequency Mode can be Forced by an External Pin
- Trickle Charge System for Deeply Discharged Batteries
 - Automatic Trickle Charge Current (256mA)
 - Holds Minimum Voltage to System
- SMBus 2-Wire Serial Interface
- Default System Voltage Values for 1-Cell, 2-Cell or 3-Cell Operation Selected by an External Pin
- Adapter In-rush FET Control
- Adapter Isolation FET Control
- Battery Short Circuit Protection
- Fast System-Load Transient Response
- Monitor Outputs
 - Adapter Current (2.5% Accuracy)
 - AC-adapter Present Indicator
- 11-Bit Max System Voltage Setting
- 7-Bit Min System Voltage Setting
- 6-Bit Charge Current Setting
 - Over 8A Battery Charger Current
- 6-Bit Adapter Current Setting
 - Over 8A Adapter Current
- +4.5V to +22V Adapter Voltage Range
- Pb-Free (RoHS Compliant)

Applications

- Notebook Computers
- Tablet PCs
- Portable Equipment with Rechargeable Batteries

© Copyright Intersil Americas LLC 2009-2012. All Rights Reserved.
All trademarks and registered trademarks are the property of their respective owners.

For additional products, see www.intersil.com/en/products.html

Intersil products are manufactured, assembled and tested utilizing ISO9001 quality systems as noted
in the quality certifications found at www.intersil.com/en/support/qualandreliability.html

Intersil products are sold by description only. Intersil may modify the circuit design and/or specifications of products at any time without notice, provided that such modification does not, in Intersil's sole judgment, affect the form, fit or function of the product. Accordingly, the reader is cautioned to verify that datasheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.

For information regarding Intersil Corporation and its products, see www.intersil.com