




8
7
6
5
4
3
2
1
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 4474: ADDED 1.0 FT. LENGTH, UPDATED FORMAT, ADDED NOTES	1/7/10	D. CASTRO
-	-	-	-
-	-	-	-
-	-	-	-



"P1"
15-PIN MALE
D-SUB CONNECTOR
GOLD PLATED PINS



"J1"
15 CONTACT FEMALE
D-SUB CONNECTOR
GOLD PLATED CONTACTS

WIRING MAP		
"P1"	WIRE COLOR	"J1"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	PURPLE	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK / WHITE	13
14	BROWN / WHITE	14
15	RED / WHITE	15
SHELL	DRAIN WIRE	SHELL

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

PART NUMBER	LENGTH	
	FEET	METERS
CSMN15MF-1	1	0.31
CSMN15MF-2.5	2.5	0.76
CSMN15MF-5	5	1.52
CSMN15MF-10	10	3.05
CSMN15MF-15	15	4.57
CSMN15MF-25	25	7.62
CSMN15MF-50	50	15.24

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-COM [®] Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 CATEGORY DATA CABLING
OVERALL CABLE LENGTH TOLERANCE: <12 [305] = ±1 [25] / -0 >12 [305] <60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	DRAWN BY TJC	6/6/01	
	CHECKED BY DFP	7/18/01	
	APPROVED BY CM	7/19/01	
ALL OTHER DIMENSIONAL TOLERANCES: $X = \pm .2$ $XX = \pm .02$ $XXX = \pm .005$	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION DELUXE MOLDED CABLE, DB15M TO DB15F
PROJECTION	COLOR VARIATIONS MAY OCCUR		SIZE A FSCM NO. 43321 DWG. NO. CSMN15MF REV. E
	CSMN-FS01		SCALE: NONE CAD FILE: CSMN15MF.SLDDRW SHEET 1 OF 1