


D-SUB METAL HOOD

Variable cable entries – 9-50 pos. – Slide lock




RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784

DESCRIPTION



- Zinc die-cast hood, EMI/RFI shielding
- Design:
 - 9 pos. = two sided cable entries,
 - 15-50 pos. = three cable entries
- Delivery includes: Hood, blanking plugs, screws for assembly, grounding screw, slide lock, spring
- Cable clamp must be ordered separately
- Crimp fitting and crimp tool please contact factory
- Bulk or single packaged units

PRODUCT DRAWING

9 pos.



15-50 pos.



No. of pos.	A	B	C	Ø D
09	32.00	25.00	14.80	12.10
15	39.30	33.30	14.80	12.10
25	53.20	47.04	14.80	12.10
37	69.50	63.50	14.80	12.10
50	67.00	61.10	17.80	14.60

ORDER DATA

D-SUB METAL HOOD – VARIABLE CABLE ENTRIES			D-SUB METAL HOOD – CABLE CLAMP – SLIDE LOCK		
No. of pos.	Design	Part Number	No. of pos.	Design	Part Number
09	Housing/Two side cable entries	165 X 11659 X	09-37	Cable clamp	160 X 11189 X
15	Housing/Three cable entries	165 X 11669 X	50	Cable clamp	160 X 11199 X
25	Housing/Three cable entries	165 X 11679 X	09-37	Locking hooks for slide lock	165 X 10119 X
37	Housing/Three cable entries	165 X 11689 X	50	Locking hooks for slide lock	165 X 10129 X
50	Housing/Three cable entries	165 X 11699 X			

For single packaged add the letter „E“ at the end of the part number.