

Digital Sound Level Meters

✓ **Two models for general purpose and high accuracy Type II measurements**
With 1.5dB or 2dB accuracy

Features:

- A and C weighting
- High and Low measuring ranges:
Model 407735 - Low (35 to 100dB), High (65 to 130dB)
Model 407736 - Low (35 to 90dB), High (75 to 130dB)
- 0.1dB resolution
- Fast/slow response
- Max Hold with reset button
- Model 407736 meets ANSI and IEC 651 Type II standards
- Large 0.5" 3-1/2 digit LCD display
- Built-in calibration check (94dB)
- Tripod mount and analog DC/AC conditioned outputs of 10mV/dB
- Utilizes 0.49"(12.3mm) condenser microphone
- Dimensions: 9.5 x 2.7 x 1" (241 x 69 x 25mm)
Weight: 7.6 oz (215g)
- Complete with hard vinyl case and 9V battery



Optional 94/114dB
Calibrator

Ordering Information:

407735.....Digital Sound Level Meter, 2dB accuracy
407735-NIST407735 with NIST Certificate
407736.....Digital Sound Level Meter, 1.5dB accuracy
407736-NIST407736 with NIST Certificate
407766.....94/114dB Sound Level Calibrator
40705X.....AC/DC Recorder Output Cable



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Extech:

407736 407736-NIST