




## IN SERIES ADAPTERS

| Description                               | Dimensions, inches (millimeters) |             | Body  | Contact | Amphenol                | Fig. |
|-------------------------------------------|----------------------------------|-------------|-------|---------|-------------------------|------|
|                                           | a                                | b           |       |         |                         |      |
| Straight Adapter Jack-Jack                | 1.28 (32.5)                      | .437 (11.1) | Brass | P7      | <a href="#">31-4791</a> | 1    |
| Right Angle Adapter Jack to Plug          | 1.03 (26.1)                      | .625 (15.9) | Brass | P7      | <a href="#">79125</a>   | 2    |
| Tee Adapter Jack-Plug-Jack                | 1.28 (32.5)                      | .96 (24.4)  | Brass | P7      | <a href="#">79700</a>   | 3    |
| Bulkhead Adapters (pressurized) Jack-Jack | 1.41 (35.8)                      | .750 (19.1) | Brass | P7      | <a href="#">79100</a>   | 4    |