

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® STR-M	12.09.2012

For the benefits, refer to SKINTOP® ST-M



Info

Now with IP 69 K approval! Proven to withstand the most demanding cleaning procedures for industrial machinery with high-pressure cleaners and hot water!

Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Design

Metric connection thread acc. to EN 50262

Approvals (Norm references)

UL File Nr. E79903

Note

Refer to SKINTOP® metric accessories for suitable accessories

Counter nut to be used: SKINTOP® GMP-GL-M

SKINTOP® STR M ISO types have an extra-long connection thread

SKINTOP® STR M ISO versions with extra-long connection thread, see table, no

DNV approval

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Caution:

Refer to Appendix T21 for the installation dimensions and torques

Colour delivered:

Silver grey (RAL 7001)
Light grey (RAL 7035)
Black (RAL 9005), UV-resistant

Material:

Body: Polyamide
Seal: CR

Tests:

GGVS: TÜ.EGG.020-95

Protection rating:

IP 68 - 5 bar
IP 69 K

Temperature range:

Fixed: -40°C to +100°C
Dynamic: -20°C to +80°C



Product Management	Document: LAPP_PRO977EN.pdf	1 / 4
--------------------	-----------------------------	-------


SKINTOP® STR-M

12.09.2012

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length inner mm	Pieces / PU
SKINTOP® STR-M silver grey						
53111100	STR-M 12 x 1,5	1-5	15	30.0	8.0	100
53111110	STR-M 16 x 1,5	2-7	19	34.0	8.0	100
53111120	STR-M 20 x 1,5	5-10	25	37.0	9.0	100
53111130	STR-M 25 x 1,5	6-13	30	40.0	10.0	50
53111140	STR-M 32 x 1,5	7-15	36	47.0	10.0	25
53111150	STR-M 40 x 1,5	15-23	46	52.0	10.0	10
53111160	STR-M 50 x 1,5	22-29	55	62.0	12.0	5
53111170	STR-M 63 x 1,5	28-39	66	71.0	12.0	5
SKINTOP® STR-M black						
53111300	STR-M 12 x 1,5	1-5	15	30.0	8.0	100
53111310	STR-M 16 x 1,5	2-7	19	34.0	8.0	100
53111320	STR-M 20 x 1,5	5-10	25	37.0	9.0	100
53111330	STR-M 25 x 1,5	6-13	30	40.0	10.0	50
53111340	STR-M 32 x 1,5	7-15	36	47.0	10.0	25
53111350	STR-M 40 x 1,5	15-23	46	52.0	10.0	10
53111360	STR-M 50 x 1,5	22-29	55	62.0	12.0	5
53111370	STR-M 63 x 1,5	28-39	66	71.0	12.0	5
SKINTOP® STR-M light grey						
53111500	STR-M 12 x 1,5	1-5	15	30.0	8.0	100
53111510	STR-M 16 x 1,5	2-7	19	34.0	8.0	100
53111520	STR-M 20 x 1,5	5-10	25	37.0	9.0	100
53111530	STR-M 25 x 1,5	6-13	30	40.0	10.0	50
53111540	STR-M 32 x 1,5	7-15	36	47.0	10.0	25
53111550	STR-M 40 x 1,5	15-23	46	52.0	10.0	10
53111560	STR-M 50 x 1,5	22-29	55	62.0	12.0	5
53111570	STR-M 63 x 1,5	28-39	66	71.0	12.0	5
SKINTOP® STR M ISO silver-grey (with long metric connecting thread)						
53017110	STR M 16 x 1,5	2-6	19	40.0	12.0	100
53017130	STR M 20 x 1,5	4-9	24	45.0	13.0	100

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length inner mm	Pieces / PU
53017140	STR M 25 x 1,5	6-12	27	47.0	13.0	50
SKINTOP® STR M ISO black (with long metric connecting thread)						
53017310	STR M 16 x 1,5	2-6	19	40.0	12.0	100
53017330	STR M 20 x 1,5	4-9	24	45.0	13.0	100
53017340	STR M 25 x 1,5	6-12	27	47.0	13.0	50

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
	SKINTOP® STR-M	12.09.2012



Product Management	Document: LAPP_PRO977EN.pdf	4 / 4
--------------------	-----------------------------	-------