



Heyco® Nylon Male/Female Threaded Hex Supports




4-40 x .187" MALE /
4-40 x .187" FEMALE
1/4" ACROSS FLATS

MFS4




6-32 x .250" MALE /
6-32 x .250" FEMALE
1/4" ACROSS FLATS

MFS6



8-32 x .375" MALE /
8-32 x .375" FEMALE
1/4" ACROSS FLATS

MFS8



M3 x 8,0 mm MALE /
M3 x 8,0 mm FEMALE
5,0 mm ACROSS FLATS

MFSM3

	Thread Length		Mounting Hole Diameter		Thread Length		Mounting Hole Diameter				Thread Length		Mounting Hole Diameter						
	in.	mm.	in.		in.		in.				mm.		mm.						
Male end	.187	4,8	4-40		.250 6,4		6-32		.375 9,5		8-32		Male end	8,0 .315 M3					
Female end	.187	4,8	4-40		.250 6,4		6-32		.375 9,5		8-32		Female end	8,0 .315 M3					
A		PART NO.		DESCRIPTION		PART NO.		DESCRIPTION		PART NO.		DESCRIPTION		A		PART NO.		DESCRIPTION	
in.	mm.	Natural				Natural				Natural				mm.	in.	Natural			
.250	6,4	11800		MFS4-04		11820		MFS6-04 †		11840		MFS8-04 †		10,0	.394	11860		MFSM3-M10	
.276	7,0	11801		MFS4-04.4										12,0	.472	11861		MFSM3-M12	
.312	7,9	11802		MFS4-05*		11822		MFS6-05*						15,0	.590	11862		MFSM3-M15	
.375	9,5	11803		MFS4-06		11823		MFS6-06		11843		MFS8-06 ††		18,0	.709	11863		MFSM3-M18	
.437	11,1	11804		MFS4-07		11824		MFS6-07		11844		MFS8-07		20,0	.787	11864		MFSM3-M20	
.500	12,7	11805		MFS4-08		11825		MFS6-08		11845		MFS8-08		25,0	.984	11865		MFSM3-M25	
.562	14,3	11806		MFS4-09		11826		MFS6-09		11846		MFS8-09							
.600	15,2	11807		MFS4-09.6															
.625	15,9	11808		MFS4-10		11828		MFS6-10		11848		MFS8-10							
.687	17,4					11829		MFS6-11*											
.750	19,1	11810		MFS4-12		11830		MFS6-12		11850		MFS8-12							
.875	22,2	11811		MFS4-14		11831		MFS6-14		11851		MFS8-14							
.937	23,8					11832		MFS6-15											
1.000	25,4	11813		MFS4-16		11833		MFS6-16		11853		MFS8-16							
1.125	28,6	11814		MFS4-18		11834		MFS6-18		11854		MFS8-18							
1.250	31,8	11815		MFS4-20		11835		MFS6-20		11855		MFS8-20							
1.312	33,3					11836		MFS6-21											
1.375	34,9	11817		MFS4-22		11837		MFS6-22		11857		MFS8-22							
2.000	50,8	11818		MFS4-32		11838		MFS6-32		11858		MFS8-32							

Standard color natural.

† Female thread depth is .190" (4,8 mm)

†† Female thread depth is .200" (5,1 mm)

* Special order.

*Quick
Specs*

Material Nylon 6/6
Flammability Rating 94V-2
Temperature Range -40°F (-40°C) to 185°F (85°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3330](#) [3332](#) [3340](#) [3380](#) [3328](#) [3324](#) [3325](#) [3329](#) [3327](#) [3346](#) [3393](#) [3326](#) [3303](#) [3373](#) [3378](#) [3352](#) [3315](#) [3302](#)
[3354](#) [3308](#) [3316](#) [3355](#) [3334](#) [3314](#) [3375](#) [3356](#) [3379](#) [3382](#) [3342](#) [3313](#) [3317](#) [3376](#) [3362](#) [3374](#) [3306](#) [3353](#)
[3364](#) [3305](#) [3304](#) [3363](#) [3372](#) [3312](#) [3331](#)