

SNP2210C2



Article Number: 190-00113

Snapper Hose Clamps, .918"/1.049" Min/Max Diameter, POM, White, 100/pkg

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	SNP2210C2
Type	SNP22
Color	White (WH)
Features and Benefits	• Designed for quick, ratcheted installation and can be released and reused. • Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.
Product Description	HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.
Short Description	Snapper Hose Clamps, .918"/1.049" Min/Max Diameter, POM, White, 100/pkg

Product Dimensions

Fixation Method	Plug-in mounting
Variant	Closed
Width W2 (Imperial)	0.232 "
Width W2 (Metric)	5.89 mm
Diameter Min. (Imperial)	0.918 "
Diameter Min. (Metric)	23.32 mm
Diameter Max. (Imperial)	1.049 "
Diameter Max. (Metric)	26.64 mm
Wall Thickness WT (Imperial)	0.07 "
Wall Thickness WT (Metric)	1.8 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100
Carton Quantity	2000

Material and Specifications

Material	Polyacetal (POM)
Material Shortcut	POM
Flammability	UL94 HB
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes

