


LABEL AND PRINT TECHNOLOGY INDEX BY SIZE

- F** Freezer environment
- N** Liquid nitrogen environment
- A** Autoclave environment
- H** Hot water (100°C) baths
- S** Self-laminating label
- L** Low-profile (extremely thin) label
- R** Removable



PART NUMBER EXPLANATION:

Most Brady part numbers for printable labels follow the same three-part format:

The first code indicates the technology, the second part is a number indicating the die size used (where applicable) and the third part indicates the Brady material used (where applicable).

PTL-82-499
 TLS2200 technology
 Die # 82, 0.375" dia. x 0.375" dia. Material B-499, Nylon Cloth

THT-143-499
 Thermal Transfer technology
 Die # 143, 0.375" dia. x 0.375" dia. Material B-499, Nylon Cloth

LAT-60-799
 Laser Printable technology
 Die # 60, 0.375" dia. x 0.375" dia. Material B-799, Nylon Cloth

Diagram	Portable Printer Part Number	Thermal Transfer Printer Part Number	Laser Printer Part Number	Label Width A Inch (mm)	Label Height B Inch (mm)	Write-On Area / Diameter C Inch (mm)	Special Properties
0.375" Label Diameter							
●	PTL-82-499	THT-143-499-3	LAT-60-799-2.5			0.375 (9.525) dia.	FNA
●	PTL-82-499-YL					0.375 (9.525) dia.	FNA
0.500" Label Diameter							
●	PTL-83-499	THT-144-499-3	LAT-61-799-2.5	0.500 (12.70) dia.		0.500 (12.70) dia.	FNA
●	PTL-83-499-YL			0.500 (12.70) dia.		0.500 (12.70) dia.	FNA
0.500" Label Width							
▲	PTL-7-423			0.500 (12.70)	0.500 (12.70)		F A
▲	PTL-8-430			0.500 (12.70)	50.000 ft (15 m)		F A
0.750" Label Width							
▲	PTL-11-498			0.750 (19.05)	0.500 (12.70)		F R
▲	PTL-11-499	THT-68-499-3	LAT-40-799-1	0.750 (19.05)	0.500 (12.70)		FNA
0.900" Label Width							
▲	PTL-84-499	THT-125-499-3		0.900 (22.86)	0.500 (12.70)		FNA
X		THT-126-499-3		0.900 (22.86)	0.500 (12.70)	0.500 (12.70) dia.	FNA
▲	PTL-80-424			0.900 (22.86)	0.750 (19.05)		F
▲	PTL-80-488	THT-140-488-3		0.900 (22.86)	0.750 (19.05)		F A
▲	PTL-97-488	THT-141-488-3		0.900 (22.86)	0.900 (22.86)		F A
1.000" Label Width							
▲	PTL-14-423	THT-41-423-10		1.000 (25.40)	0.187 (4.75)		F A
▲	PTL-15-423	THT-51-423-10		1.000 (25.40)	0.250 (6.35)		F A
▲	PTL-16-498			1.000 (25.40)	0.375 (9.53)		F R
▲	PTL-16-499	THT-152-499-3	LAT-8-799-10	1.000 (25.40)	0.375 (9.53)		FNA
X	PTL-98-499			1.000 (25.40)	0.375 (9.53)	0.375 (9.53) dia.	FNA
▲	PTL-17-423	THT-5-423-10		1.000 (25.40)	0.500 (12.70)		F A
▲	PTL-17-430			1.000 (25.40)	0.500 (12.70)		F A
▲	PTL-17-498			1.000 (25.40)	0.500 (12.70)		F R
▲	PTL-17-499			1.000 (25.40)	0.500 (12.70)		FNA
▲	PTL-17-449		LAT-7-709-10	1.000 (25.40)	0.500 (12.70)		F A R
▲	PTL-17-351	THT-5-351-10		1.000 (25.40)	0.500 (12.70)		F
▲			LAT-39-799-2.5	1.000 (25.40)	1.437 (36.50)		FNA
▲	PTL-42-439-OR			1.000 (25.40)	50.00 ft (15 m)		F
▲	PTL-42-439-YL			1.000 (25.40)	50.00 ft (15 m)		F

LABEL AND PRINT TECHNOLOGY INDEX BY SIZE

CONTINUED




Diagram	Portable Printer Part Number	Thermal Transfer Printer Part Number	Laser Printer Part Number	Label Width A Inch (mm)	Label Height B Inch (mm)	Write-On Area / Diameter C Inch (mm)	Special Properties
1.500" Label Width							
▶	PTL-108-461			1.500 (38.10)	0.187 (4.75)	0.700 (17.78)	FNAHSL
▲	PTL-29-498			1.500 (38.10)	0.500 (12.70)		F R
▲	PTL-29-499			1.500 (38.10)	0.500 (12.70)		FNA
▲	PTL-30-427-AW*	THT-135-427-AW-3*		1.500 (38.10)	0.750 (19.05)		FN S
▲	PTL-30-499	THT-136-499-3		1.500 (38.10)	0.750 (19.05)		FNA
▲	PTL-31-351			1.500 (38.10)	1.000 (25.40)		F
▲	PTL-31-423			1.500 (38.10)	1.000 (25.40)		F A
▲	PTL-31-498			1.500 (38.10)	1.000 (25.40)		F R
▲	PTL-31-499			1.500 (38.10)	1.000 (25.40)		FNA
1.625" Label Width							
▶	PTL-76-461	THT-133-461-3	LAT-56-361-2.5	1.625 (41.275)	0.600 (15.24)	1.000 (25.40)	FNAHSL
1.800" Label Width							
▶	PTL-73-461	THT-123-461-3	LAT-57-361-2.5	1.800 (45.72)	0.375 (9.52)	0.750 (19.05)	FNAHSL
▶	PTL-72-461	THT-122-461-3		1.800 (45.72)	0.500 (12.70)	0.750 (19.05)	FNAHSL
1.875" Label Width							
▶			LAT-10-747-10	1.875 (47.62)	0.250 (6.35)		F A
1.900" Label Width							
▲	PTL-81-488			1.900 (48.26)	0.250 (6.35)		F A
▲	PTL-81-499			1.900 (48.26)	0.250 (6.35)		FNA
▲	PTL-78-427-AW*			1.900 (48.26)	1.000 (25.40)		FN S
▲	PTL-78-499			1.900 (48.26)	1.000 (25.40)		FNA
▲	PTL-78-488			1.900 (48.26)	1.000 (25.40)		F A
2.000" Label Width							
▲	PTL-2-423	THT-15-423-2.5		2.000 (50.80)	0.250 (6.35)		F A
▲		THT-151-499-3		2.000 (50.80)	0.250 (6.35)		FNA
▲	PTL-20-423	THT-17-423-3		2.000 (50.80)	1.000 (25.40)		F A
▲	PTL-20-351	THT-17-351-3		2.000 (50.80)	1.000 (25.40)		F
▲		THT-137-427-AW-3*		2.000 (50.80)	1.000 (25.40)		FN S
▲		THT-137-499-3		2.000 (50.80)	1.000 (25.40)		FNA
2.200" Label Width							
▶	PTL-74-427	THT-127-427-3		2.200 (55.88)	0.500 (12.70)	0.750 (19.05)	FN S
▶	PTL-74-461	THT-127-461-3		2.200 (55.88)	0.500 (12.70)	0.750 (19.05)	FNAHSL
2.500" Label Width							
▲		THT-142-423-2.5		2.500 (63.50)	0.200 (5.08)		F A
2.625" Label Width							
▶	PTL-86-461	THT-153-461-3	LAT-59-361-2.5	2.625 (66.675)	0.600 (15.24)	1.000 (25.40)	FNAHSL
▶	PTL-75-427	THT-131-427-3		2.625 (66.675)	1.000 (25.40)	1.000 (25.40)	FN S
▶	PTL-75-461	THT-131-461-3	LAT-58-361-1	2.625 (66.675)	1.000 (25.40)	1.000 (25.40)	FNAHSL
▶	BPTL-75-461			2.625 (66.675)	1.000 (25.40)	1.000 (25.40)	FNAHSL
▶	PTL-75-461-YL			2.625 (66.675)	1.000 (25.40)	1.000 (25.40)	FNAHSL
3.000" Label Width							
▲	PTL-22-423			3.000 (76.20)	1.000 (25.40)		F A
▲	PTL-37-351			3.000 (76.20)	1.900 (48.26)		F
3.500" Label Width							
▶	PTL-77-461	THT-134-461-3		3.500 (88.90)	1.500 (38.10)	1.250 (31.75)	FNAHSL
3.750" Label Width							
▶	PTL-79-461			3.750 (95.25)	0.750 (19.05)	1.000 (25.40)	FNAHSL
▶		THT-10-427-3		3.750 (95.25)	1.000 (25.40)	1.000 (25.40)	FN S
5.250" Label Width							
▶		THT-139-461-2		5.250 (133.35)	1.000 (25.40)	1.500 (38.10)	FNAHSL

* The label is all white.